


R76, Film, Double Metallized Polypropylene, Automotive Grade, 0.22 uF, 5%, 400 VDC, 85°C, Lead Spacing = 15mm



General Information

Supplier:	KEMET
Series:	R76
Dielectric:	Double Metallized Polypropylene
Style:	Radial
Features:	Automotive Grade, Pulse
RoHS:	Yes
Lead:	Wire Leads
Qualifications:	AEC-Q200
AEC-Q200:	Yes

Dimensions

L	18mm +0.5mm
H	16mm +0.1mm
T	10mm +0.2mm
S	15mm +/-0.4mm
LL	30mm +5mm
F	0.8mm +/-0.05mm

Packaging Specifications

Packaging:	Bulk, Bag
Packaging Quantity:	500

Specifications

Capacitance:	0.22 uF
Capacitance Tolerance:	5%
Voltage AC:	250 VAC
Voltage DC:	400 VDC
Temperature Range:	-55/+110°C
Rated Temperature:	85°C
Dissipation Factor:	0.03% 1kHz, 0.06% 10kHz
Insulation Resistance:	100 GOhms
Max dV/dt:	900 V/us
Resistance:	11.57 mOhms (25kHz)
Ripple Current:	8.64 Amps (25kHz 60C), 198 Amps (Peak)
Inductance:	10 nH