

# VS-25-BU-DSUB-CD-G - D-SUB contact support




1689941

<https://www.phoenixcontact.com/gb/products/1689941>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

D-SUB contact carrier, shell size 3, for 25 signal contacts, type of contact socket, for crimp contacts, straight, fixing with M3 thread, for panel mounting frame VS-25-...



## Commercial data

Item number	1689941
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	ABNCAB
Product key	ABNCAB
Catalog page	Page 212 (C-2-2013)
GTIN	4017918914349
Weight per piece (including packing)	16.17 g
Weight per piece (excluding packing)	16.17 g
Customs tariff number	85366990
Country of origin	DE

## Technical data

### Product properties

Product type	Contact insert
Type	D-SUB
Number of positions	25
Connection profile	D-SUB
Number of slots	1
Type	Socket
Shielded	yes

### Insulation characteristics

Overvoltage category	III
Degree of pollution	2

### Electrical properties

Rated voltage in acc. with IEC 61076-2-101	400 V
Rated voltage (III/3)	125 V
Rated current	5 A (at 20 °C)
Test voltage	1200 V
Transmission medium	Copper

### Connection data

Connection method	Crimp connection
-------------------	------------------

### Dimensions

Width	18.1 mm
Height	12.93 mm
Length	53.42 mm

### Material specifications

Flammability rating according to UL 94	V0
Housing material	Metal
Housing surface material	metal-plated
Contact material	Copper alloy
Contact surface material	Gold
Contact carrier material	Glass-fiber reinforced thermoplastics, UL 94 V0

### Mechanical properties

#### Mechanical data

Insertion/withdrawal cycles	≥ 500
Insertion force per signal contact	≤ 3.40 N

### Environmental and real-life conditions

# VS-25-BU-DSUB-CD-G - D-SUB contact support



1689941

<https://www.phoenixcontact.com/gb/products/1689941>

## Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-55 °C ... 130 °C

## Mounting

Mounting type	Screw mounting
---------------	----------------

# VS-25-BU-DSUB-CD-G - D-SUB contact support



1689941

<https://www.phoenixcontact.com/gb/products/1689941>

## Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1689941>



**UL Recognized**

Approval ID: E118976

# VS-25-BU-DSUB-CD-G - D-SUB contact support



1689941

<https://www.phoenixcontact.com/gb/products/1689941>

## Classifications

### ECLASS

ECLASS-13.0	27440302
-------------	----------

### ETIM

ETIM 9.0	EC001132
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

1689941

<https://www.phoenixcontact.com/gb/products/1689941>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(a), 6(a)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	78832de1-e881-4b7b-bfce-de4900ae908a

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)