

FEATURES

- Maximum operating temperature of 105°C
- A voltage rating of 600 / 1000 V
- Single-core cable design
- Flame retardant

RS PRO White Single Core Tri-rated Cable, 4mm² CSA, 1kV, 41A, 100m

RS Stock No.: 815-8703



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

From RS PRO, comes a range of high quality and great value Tri-rated cables. Manufactured with a premium copper conductor and insulated with PVC (Polyvinyl Chloride), these Tri-rated cables are a fantastic solution for use in control panels and other types of electrical equipment

General Specifications

Type	Single Core
Tri-rated	Yes
Sheath Colour	Grey
Fire Behaviour	Flame Retardant
Application	Electrical cabinets, Industrial electrical installations, Small electronic devices, Relay and instrumentation panels, Control metering, Motor starters

Electrical Specifications

Voltage Rating	1kV
Current Rating	136A
Conductor Material	Copper
Insulation Material	PVC

Mechanical Specifications

Length	100m
Cross Sectional Area	25mm ²
Outer Diameter	10.6mm
American Wire Gauge	4
Core Strands	196/0.4mm
Size of Strands	0.4mm
Insulation Wall Thickness	1.6mm

Operation Environment Specifications

Operating Temperature Range	-15°C to 105°C
Minimum Operating Temperature	-15°C
Maximum Operating Temperature	105°C

Approvals

Compliance/Certifications	CSA / UL / BS6231
Standards Met	CSA C22.2 Type TEW, UK BS 6231, UL 1283

AWM Size	Size (mm ²)	Max diam of wires in conductor mm	Maximum resistance at 20°C Ω /Km	UL Style	Nominal R/T(mm)	Nominal Diam (mm)	Current Rating (A)	Weight (Kg/km)
22	0.5	0.21	39.0	1015	0.8	2.6	11	11
20	0.75	0.21	26.0	1015	0.8	2.8	14	14
18	1	0.21	19.5	1015	0.8	3	17	17
16	1.5	0.26	13.3	1015	0.8	3.3	21	22
14	2.5	0.26	7.98	1015	0.8	3.7	30	33
12	4	0.31	4.95	1015	0.8	4.3	41	49
10	6	0.31	3.30	1015	0.8	5.1	53	71
8	10	0.41	1.91	1028	1.2	6.8	75	124
6	16	0.41	1.21	1283	1.58	9.2	100	199
4	25	0.41	0.78	1283	1.58	10.6	136	290
2	35	0.41	0.554	1283	1.58	11.6	167	387
1	50	0.41	0.386	1284	2.1	14.4	190	570
2/0	70	0.51	0.272	1284	2.1	16.5	240	781
3/0	95	0.51	0.206	1284	2.1	18.7	300	1025
4/0	120	0.51	0.121	1284	2.1	20	340	1280