

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

19007-0082

Status:

Active

Overview:

Standard Quick-Disconnect Terminals

Description:

InsulKrimp™ Female Fully Insulated Quick Disconnect Flag for 10-12 AWG Wire, Tab 6.35 x 0.81mm, 94 V-0 Material

Documents:

3D Model

Drawing (PDF)

Product Specification PS-19902-008 (PDF)

Product Specification PS-19902-011 (PDF)

Product Specification PS-19902-013 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E79133

General

Product Family

Quick Disconnects

Series

19007

Crimp Quality Equipment

Yes

Insulated

Fully

Overview

Standard Quick-Disconnect Terminals

Product Name

InsulKrimp™

Type

Quick Disconnect

UPC

800756386744

Physical

Barrel Type

Closed

Color - Resin

Yellow

Flammability

94V-0

Gender

Female

Glow-Wire Compliant

Yes

Insulation

Nylon (PA)

Lock to Mating Part

None

Material - Metal

Brass

Material - Plating Mating

Tin

Material - Plating Termination

Tin

Material - Resin

Nylon

Net Weight

1.615/g

Orientation

Flag

Packaging Type

Bag

Polarized to Mating Part

No

Tab Thickness

0.81mm

Tab Width

6.35mm

Temperature Range - Operating

-65°C to +105°C

Wire Insulation Diameter

6.60mm

Wire Size AWG

10 (105 strands), 12 (65 strands)

Wire Size mm²

2.70 - 6.60

Electrical

Voltage - Maximum

600V

Material Info

Old Part Number

C-2211V

Reference - Drawing Numbers

Product Specification

PS-19902-008, PS-19902-011, PS-19902-013

Sales Drawing

SD-19007-002




image - Reference only

Series

EU RoHS

ELV and RoHS Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

19007Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Hand Crimp Tool	0640012800
Crimp Head for the AT-200™ Pneumatic Hand Tool	0640052800

This document was generated on 02/24/2015

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION