



GE
Lighting



Rough Service GLS - Frosted

TU 100A1/GRS-FR/BC 200-250V GE 1/20
MIH

31635

Product information

GE incandescent lamps trace their ancestry to the world's first practical electric bulb, invented by Thomas Alva Edison, founder of General Electric Company, in 1879.

Available in all shapes and sizes, they offer particular qualities of light to suit specific applications.



Product data

Cap/Base	B22d
Bulb Shape	PS
Bulb Finish	Diffuse
Bulb Diameter [mm]	60
Nominal Length [mm]	103.5
Net weight per piece [g]	30
Gross weight per piece [g]	58
Brand	General Electric (GE)

Performance data

Nominal correlated colour temperature (CCT) [K]	0.1
Nominal lumens [lm]	880
Rated efficacy [lm/W]	8.8
Energy efficiency class (EEC)	E
Rated Life [h]	3000
Nominal power [W]	100
Nominal lamp voltage [V]	240

Electrical data

Weighted energy consumption [kWh/1000h]	100.37
Dimming Capability	Yes

Logistic data

DUN Code	05021731316357
EAN Code	5021731316357
Pack Quantity	20
Inner pack type	BOX
Layer quantity	220 EUR, 300 UK
Layer quantity EUR	220
Layer quantity UK	300
Pallet quantity EUR (PC)	1980
Pallet quantity UK (PC)	2700
Outer case size	308 x 248 x 121 (mm)
Product status	Available

Downloads & Links

[Go to the catalog site \(HTTP\)](#)

[Incandescent Lamps Spectrum Catalogue \(PDF\)](#)

[Lighting design tools & calculators \(HTTP\)](#)