

Junction box

Abox Pro 060-L



Abox Pro 060-L

Junction box

CUSTOMIZABLE

Productnumber: 40640001

Dimensions: 127 x 127 x 75 mm

Junction box, protection class IP66/IP67/IP69, nominal cross-section 6 mm², certified by VDE (DIN EN 60670-1/-22 (VDE 0606-1/-22)), DLG (Ammonia resistance), DNV (Class: Ships and Offshore Installations), knockouts, M20/M32, (1 rear, 7 side), internal fixing points, for installation in industrial environments and unprotected outdoor areas

grey, Ui=1000 V AC, without terminals

Accessories supplied:

4 double membrane seals IP66 M32 sealing range 13 - 21 mm, cover retainer



Technical Data

electrical characteristics

Rated insulation voltage AC:	1000 V
Rated insulation voltage DC:	1000 V
Max. conductor cross section:	6 mm²
Protection class:	II
Type of protection:	IP66/IP67/IP69
Terminal type:	none

Colours

Base unit colour:	grey
Cover colour:	grey

Dimensions

Width:	127 mm
Length:	127 mm
Height:	75 mm
Inner length:	113 mm
Inner width:	113 mm
Inner height:	55 mm
Weight:	0.3075 kg

Material characteristics

UV-resistant:	yes
Halogen free:	yes
Flammability class according with UL94:	V0
Glow-wire flammability according to EN 60695-2-11:	960 °C

Max. number of terminals per cross section acc. to DIN VDE 0606-1

max. amount of terminals at 1,5²:	14
max. amount of terminals at 2,5²:	10

Max. number of terminals per cross section acc. to DIN VDE 0606-1

max. amount of terminals at 4²:	8
max. amount of terminals at 6²:	5

Max. number of wires per cross section acc. to DIN VDE 0606-1

max. amount of wires at 1,5²:	40
max. amount of wires at 2,5²:	30
max. amount of wires at 4²:	24
max. amount of wires at 10²:	15

mechanical properties

Impact strength:	IK09
Sealable:	yes
Cover screw torque:	1.5 Nm
Type of fastening:	Wall/ceiling mounting
Fastening:	internal fixing points

Ambient conditions

max. relative humidity 25°C:	95 %
max. relative humidity 40°C:	50 %
Min. ambient temperature:	-35 °C
Max. ambient temperature:	80 °C
24h ambient temperature:	60 °C
Installation location:	unprotected outdoor areas

Sales Information

EAN:	4013902664276
ETIM Class:	EC002600
Custom tariff number:	85389099
MOQ:	1

Material

Base unit material:	Polycarbonate, glass-fibre reinforced
Cover material:	Polycarbonate
Sealing material:	Thermoplastic elastomer
Cover screw material:	Stainless steel V2A

Certificates

Test mark:	VDE (DIN EN 60670-1/-22 (VDE 0606-1/-22))
Test mark:	DLG (Ammonia resistance)
Test mark:	DNV (Class: Ships and Offshore Installations)

Accessories

[22742001 - KVR M20-MGM - Cable gland](#)

[22742101 - KVR M20-GDB/MGM - Cable gland](#)

[22743201 - KVR M32-MGM - Cable gland](#)

[26042001 - DMS M20 - Double-membrane seals](#)

[26043201 - DMS M32 - Double-membrane seals](#)

[89510601 - Abox MPI 060 - Mounting plate](#)

[89530601 - Abox 060 NS35 - Standard rail](#)

[89600401 - Abox 060 KH 221 4² - Terminal holder](#)

[89640601 - Abox 060 KLS-6² - Terminal block](#)

[89602001 - MABF 100-1 - Mast/pipe fixing set](#)

Cable gland

