

# SAC-6P-DTMS-5P-M12FS VA - Adapter



1088172

<https://www.phoenixcontact.com/in/products/1088172>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Adapter, 5-position, Plug straight DEUTSCH DT04-6P, on Socket straight M12, coding: A



## Commercial data

Item number	1088172
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	*****
Product key	AF1GGA
GTIN	4055626888521
Weight per piece (including packing)	26.3 g
Weight per piece (excluding packing)	26.3 g
Customs tariff number	85444290
Country of origin	US

# SAC-6P-DTMS-5P-M12FS VA - Adapter



1088172

<https://www.phoenixcontact.com/in/products/1088172>

## Technical data

### Notes

Note on application	Sufficient strain relief at the connection point can prevent premature stress and wear. Utilize tie down accessories to eliminate bending and dynamic loads on the connector.
---------------------	---

### Product properties

Product type	M8/M12 adapters
Number of positions	5
Coding	A

#### Insulation characteristics

Overvoltage category	II
Degree of pollution	3

### Electrical properties

Nominal voltage $U_N$	48 V AC
	60 V DC
Nominal current $I_N$	4 A

### Material specifications

Flammability rating according to UL 94	V0
Seal material	Viton
Material of grip body	GF nylon
Contact material	CuSn
Contact surface material	Ni/Au M12, Ni/Sn DT
Contact carrier material	GF nylon
Material for screw connection	Stainless steel

### Connector

#### Connection 1

Type	Plug straight DEUTSCH DT04-6P
Number of positions	5

#### Connection 2

Type	Socket straight M12
Number of positions	5
Coding type	A

### Mechanical properties

#### Mechanical data

Insertion/withdrawal cycles	$\geq 100$
-----------------------------	------------

### Environmental and real-life conditions

# SAC-6P-DTMS-5P-M12FS VA - Adapter



1088172

<https://www.phoenixcontact.com/in/products/1088172>

## Ambient conditions

Degree of protection	IP67
	IP69K
Ambient temperature (operation)	-40 °C ... 105 °C

## Approvals

### National Marine Electronics Association

Certificate	approved
-------------	----------

## Standards and regulations

Standard designation	M12 connector
Standards/specifications	IEC 61076-2-101
Standards/specifications	SAE J2030


# SAC-6P-DTMS-5P-M12FS VA - Adapter

1088172

<https://www.phoenixcontact.com/in/products/1088172>



## Drawings

Schematic diagram




DEUTSCH DT04-5P pin assignment

Dimensional drawing



DT/M12 adapter

Schematic diagram



Pin assignment M12 socket, 5-pos., A-coded, view female side

Circuit diagram



Contact assignment

# SAC-6P-DTMS-5P-M12FS VA - Adapter



1088172

<https://www.phoenixcontact.com/in/products/1088172>

## Classifications

### ECLASS

ECLASS-11.0	27440106
ECLASS-12.0	27440106
ECLASS-13.0	27440106

### ETIM

ETIM 9.0	EC002925
----------	----------

### UNSPSC

UNSPSC 21.0	31251500
-------------	----------

# SAC-6P-DTMS-5P-M12FS VA - Adapter



1088172

<https://www.phoenixcontact.com/in/products/1088172>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	3084d6ba-0800-4fef-9e55-3d3675ab7c72

# SAC-6P-DTMS-5P-M12FS VA - Adapter



1088172

<https://www.phoenixcontact.com/in/products/1088172>

## Accessories

### WT-HF 3,6X140 BK - Cable tie

3240745

<https://www.phoenixcontact.com/in/products/3240745>



Cable binders for quick and secure bundling, standard version

---

### WT-BASE LS HF 4 BK - Cable binder base

3240707

<https://www.phoenixcontact.com/in/products/3240707>



Cable binder base, for cable binders up to 4 mm wide, self-adhesive (rubber) and screwable, 4 mm fixing hole, 4-sided cable binder feed-through

# SAC-6P-DTMS-5P-M12FS VA - Adapter



1088172

<https://www.phoenixcontact.com/in/products/1088172>

## EML-HA (15X9)R - Label for rough surfaces

0830600

<https://www.phoenixcontact.com/in/products/0830600>



Label for rough surfaces, Roll, white, unlabeled, can be labeled with: THERMOMARK E.300 (D)/600 (D), THERMOMARK ROLL 2.0, THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, mounting type: adhesive, Number of individual labels: 2500, text field height: 9 mm, text field width: 15 mm

---

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

[info@phoenixcontact.co.in](mailto:info@phoenixcontact.co.in)