



Moulded case
circuit breakers
P5ME

Product designation

Product type designation

Electrical features

Number of poles	Nr.	3
Rated current ($\leq 40^{\circ}\text{C}$)	A	400
Electronic overload trip adjustment range	A	150...400
Electronic short circuit trip adjustment range	A	225...4400
AC rated operation voltage U_e	V	600
Rated insulation voltage U_i	V	750
Rated impulse withstand voltage U_{imp}	kV	8
Heat dissipation per pole (max)	W	48

UL technical data

UL489 short circuit breaking capacity	240VAC 50/60Hz	kA	100
	480VAC 50/60Hz	kA	65
	600VAC 50/60Hz	kA	35
IEC60947-2 Icu short circuit breaking capacity	220...240VAC 50/60Hz	kA	100
	380...415VAC 50/60Hz	kA	65
	480...500VAC 50/60Hz	kA	35

Mechanical features

Terminals

	screw tool	M10 x 30 Allen key 7/16"
--	---------------	-----------------------------

Tightening torque for terminals

	max	Nm	54
	max	lbin	478

Mounting position

	normal allowable	On vertical plan Any
--	---------------------	-------------------------

Fixing		Screw
--------	--	-------

Weight	g	6300
--------	---	------

Mechanical life	cycles	20000
-----------------	--------	-------

Electrical life	cycles	10000
-----------------	--------	-------

Dimensions (W x H x D)	mm	140x290x110
------------------------	----	-------------

Ambient conditions

Temperature

Operating temperature

	min	$^{\circ}\text{C}$	-20
	max	$^{\circ}\text{C}$	+70

Storage temperature

	min	$^{\circ}\text{C}$	-40
	max	$^{\circ}\text{C}$	+80

Current derating for temperature $> 40^{\circ}\text{C}$


50°C	°C	375
60°C	°C	353
70°C	°C	328

Resistance & Protection


Frontal IP degree

IP20

Dimensions



Wiring diagrams



Certifications and compliance

Compliance

cULus

ETIM classification

EC000066 - Power contactor, AC switching