


## Features

- FeCu-Ni "J" Type Thermocouples
- Max. operating temperature 400°C
- ½" Fittingnut
- Protection tube AISI304(DIN1.4301) Stainless Steel
- Sensor type DIN/IEC-584 "J" FeCu-Ni
- Cable type Fiber glass+Fiber glass+Braided
- Immersion Length 50mm
- Cable Length 4meter
- Tube Diameter 8mm

## RS PRO Bayonet "J" Type Thermocouples With ½" Fittingnut

RS Stock No: 0350441



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

Standard Bayonet "J" Type Thermocouples Temperature Sensor

Diameter(M): 8mm

Immersion Length(L): 50mm

Cable Length(K): 4m

Applications Fields

- Machinery Manufacturing
- Panel Manufacturing
- Production and Test Equipment
- Food, Chemical, Textile Sectors
- Industrial Control Applications


## General Specifications

<b>Max. Operating Temperature</b>	-50 °C / +400 °C
<b>Standard cable types</b>	Fiber glass + fiber glass + braided wire
<b>Sensor type</b>	"J" Type Thermocouples (DIN/IEC-584)
<b>Protection tube material</b>	AISI304(DIN1.4301) Stainless Steel
<b>Connector</b>	½" Fittingnut

## Mechanical Specifications

<b>Diameter (M)</b>	8mm
<b>Immersion Length (L)</b>	50mm
<b>Cable Length (K)</b>	4m

## Electrical Connection



## Thermoelement Connections

