

# Eaton 259551

Catalog Number: 259551

Eaton Moeller series NZM - Molded Case Circuit Breaker.  
Undervoltage release, 60 V DC, +2early N/O, 1

### General specifications



| Product Name                     | Catalog Number       |
|----------------------------------|----------------------|
| Eaton Moeller series NZM release | 259551               |
| EAN                              | Product Length/Depth |
| 4015082595517                    | 37 mm                |
| Product Height                   | Product Width        |
| 66 mm                            | 32 mm                |
| Product Weight                   | Compliances          |
| 0.056 kg                         | UL/CSA               |
|                                  | IEC                  |
|                                  | RoHS conform         |

### Certifications

- CSA (File No. 22086)
- CSA (Class No. 1437-01)
- UL489
- UL listed
- CSA certified
- UL (Category Control Number DIHS)
- UL (File No. E140305)
- CE marking
- CSA-C22.2 No. 5-09
- IEC60947

## Product specifications

### Used with

NZM1(-4), N1(-4)

### Type

Accessory Undervoltage release Undervoltage release with early-make auxiliary contact

### Special features

Undervoltage release with 2 early-make auxiliary contacts, e.g., for early-make connection of undervoltage release in main switch applications, as well as for interlock and load shedding circuits. For use with emergency-stop devices in connection with an emergency-stop button. When the under-voltage trip is switched off, accidental contact with the circuit breaker's primary contacts is prevented when switched on. Early make of auxiliary contacts on switching on and off (manual operation): approx. 20 ms Undervoltage releases cannot be installed simultaneously with NZM...-XHIV... early-make auxiliary contact or NZM...-XA... shunt release.

### 10.10 Temperature rise

The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

### 10.11 Short-circuit rating

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

### 10.12 Electromagnetic compatibility

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

### 10.13 Mechanical function

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

### 10.2.2 Corrosion resistance

Meets the product standard's requirements.

### 10.2.3.1 Verification of thermal stability of enclosures

Meets the product standard's requirements.

### 10.2.3.2 Verification of resistance of insulating materials to normal heat

Meets the product standard's requirements.

### 10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects

Meets the product standard's requirements.

## Resources

### Brochures

[eaton-digital-nzm-brochure-br013003en-en-us.pdf](#)

[eaton-feerum-the-whole-grain-solution-success-story-en-us.pdf](#)

### Catalogs

[eaton-digital-nzm-catalog-ca013003en-en-us.pdf](#)

### Declarations of conformity

[DA-DC-03\\_NZM1](#)

### Drawings

[eaton-circuit-breaker-release-nzm-mccb-dimensions.eps](#)

[eaton-circuit-breaker-undervoltage-nzm-mccb-3d-drawing-004.eps](#)

### eCAD model

[DA-CE-ETN.NZM1-XUHIV60DC](#)

### Installation videos

[The new digital NZM Range](#)

[Introduction of the new digital circuit breaker NZM](#)

### Technical data sheets

[eaton-nzm-technical-information-sheet](#)

#### 10.2.4 Resistance to ultra-violet (UV) radiation

Meets the product standard's requirements.

#### 10.2.5 Lifting

Does not apply, since the entire switchgear needs to be evaluated.

#### 10.2.6 Mechanical impact

Does not apply, since the entire switchgear needs to be evaluated.

#### 10.2.7 Inscriptions

Meets the product standard's requirements.

#### 10.3 Degree of protection of assemblies

Does not apply, since the entire switchgear needs to be evaluated.

#### 10.4 Clearances and creepage distances

Meets the product standard's requirements.

#### 10.5 Protection against electric shock

Does not apply, since the entire switchgear needs to be evaluated.

#### 10.6 Incorporation of switching devices and components

Does not apply, since the entire switchgear needs to be evaluated.

#### 10.7 Internal electrical circuits and connections

Is the panel builder's responsibility.

#### 10.8 Connections for external conductors

Is the panel builder's responsibility.

#### 10.9.2 Power-frequency electric strength

Is the panel builder's responsibility.

#### 10.9.3 Impulse withstand voltage

Is the panel builder's responsibility.

#### 10.9.4 Testing of enclosures made of insulating material

Is the panel builder's responsibility.

#### Electric connection type

Screw connection

#### Fitted with:

Two early-make auxiliary contacts

#### Frame

NZM1

#### Minimum command time - max

15 ms

Minimum command time - min

10 ms

Number of contacts (normally open contacts)

2

Reaction time

19 ms

Pick-up power consumption at AC (undervoltage release)

1.5 VA

Pick-up power consumption at DC (undervoltage release)

0.8 W

Voltage tolerance - max

1.1

Voltage tolerance - min

.85

Rated control supply voltage

60 V DC

Rated control supply voltage (Us) at AC, 50 Hz - max

0 V

Rated control supply voltage (Us) at AC, 50 Hz - min

0 V

Rated control supply voltage (Us) at AC, 60 Hz - max

0 V

Rated control supply voltage (Us) at AC, 60 Hz - min

0 V

Suitable for

Off-load switch

Connection type

With terminal block on the left-hand switch side

Voltage type

AC

Drop-out voltage of undervoltage release AC/DC - max

0.7 x Us

Drop-out voltage of undervoltage release AC/DC - min

0.35 x Us

Terminal capacity (solid/flexible conductor)

18 - 14 AWG (1x) for undervoltage releases, off-delayed

0.75 mm<sup>2</sup> - 2.5 mm<sup>2</sup> (2x) at shunt release with ferrule  
18 - 14 AWG (2x) at shunt release  
18 - 14 AWG (2x) for undervoltage releases, off-delayed  
0.75 mm<sup>2</sup> - 2.5 mm<sup>2</sup> (1x) at shunt release with ferrule  
18 - 14 AWG (1x) at shunt release  
0.75 mm<sup>2</sup> - 2.5 mm<sup>2</sup> (1x) for undervoltage releases, off-delayed  
with ferrule  
0.75 mm<sup>2</sup> - 2.5 mm<sup>2</sup> (2x) for undervoltage releases, off-delayed  
with ferrule

**Power consumption**

0.8 W (sealing DC)  
1.5 VA (sealing AC)

**Rated control supply voltage (Us) at DC - max**

60 V

**Rated control supply voltage (Us) at DC - min**

60 V

**Number of contacts (normally closed contacts)**

0

**Number of contacts (change-over contacts)**

0

**Undelayed short-circuit release - min**

0 A

**Undelayed short-circuit release - max**

0 A

**Rated control voltage (relay contacts)**

60 V DC



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)