



Midi series are adapted for water and compressed air applications.
The wide range of plugs allows many combinations for the end-users.

- Designed for transmission of water and fluids
- High flow capabilities
- Maximum energy efficiency

own Profile

KA

Single Shut-Off


Working Pressure*:
up to 20 bar

Material:


- Coupling: Nickel plated brass
- Plug: Nickel plated brass
- Seals: NBR

Working Temperature:
-20°C up to +100°C (NBR)

Flow Rate Air:
2.200 NI/min.
inlet pressure 6 bar, pressure drop 0.6 bar




Single Shut-Off



Straight-Through

0172 Coupler with valve, Female BSPP Thread

Nickel-plated brass, NBR




DN	C		E	F	G	L
12	G3/8	0172 12 17	16	27	29	56
12	G1/2	0172 12 21	16	27	29	56


Midi Series: single shut-off = 2200NI/min

2272 Coupler without valve, Female BSPP Thread

Nickel-plated brass, NBR




DN	C		E	F	G	L
12	G1/2	2272 12 21	10	24	29	33
12	G3/4	2272 12 27	10	30	29	34.5
12	G1	2272 12 34	10	36	29	34.5



Single Shut-Off


2511 Coupler with valve, with Barb Connection for Hose

Nickel-plated brass, NBR



DN	ØD	ØD1		G	L	L1
12	12	13.5	2511 12 12	29	75	32
12	15	16.5	2511 12 15	29	75	32
12	19	20.5	2511 12 19	29	81	38


Midi Series: single shut-off = 2200NI/min



Straight-Through

2297 Coupler without valve, with Barb Connection for Hose


Nickel-plated brass, NBR



DN	ØD	ØD1		G	L	L1
12	12	13.5	2297 12 12	29	51	27
12	15	16.5	2297 12 15	29	51	27
12	19	20.5	2297 12 19	29	57	33

2294 Plug without valve, Male BSPP Thread

Nickel-plated brass




DN	C		E	F	L
12	G3/8	2294 12 17	6	22	31.5
12	G1/2	2294 12 21	9.5	22	37
12	G3/4	2294 12 27	13.5	27	41
12	G1	2294 12 34	10.5	34	36

Probe without Shut-off


0196 Plug without valve, Female BSPP Thread

Nickel-plated brass



DN	C		E	F	L
12	G1/4	0196 12 13	12	17	16
12	G3/8	0196 12 17	12	21	15
12	G1/2	0196 12 21	14	26	17


Probe without Shut-off



Straight-Through

2296 Plug without valve, Female BSPP Thread

Nickel-plated brass




DN	C		E	G	L
12	G1/2	2296 12 21	11	24	31.5
12	G3/4	2296 12 27	11	30	38
12	G1	2296 12 34	11	36	36.5

Probe without Shut-off

0195 Plug without valve, with Barb Connection for Flexible Tubing

Nickel-plated brass




DN	ØD	ØD1		F	L
12	7	9	0195 07 00	17	29.5
12	10	12.2	0195 10 00	17	29.5
12	13	15.2	0195 13 00	17	29.5
12	16	18.5	0195 16 00	21	36.5

Probe without Shut-off

2295 Plug without valve, with Barb Connection for Flexible Hose

Nickel-plated brass




DN	ØD	ØD1		G	L	L1
12	12	13.5	2295 12 12	17	48	27
12	15	16.5	2295 12 15	18	48	27
12	19	20.5	2295 12 19	24	57	33

Probe without Shut-off

2293 Y Coupler, Straight Through


Nickel-plated brass, NBR



DN		G	H
12	2293 12 00	29	27

Probe without Shut-off


Midi Series: straight-through = 2200 NI/min



Straight-Through

2270 Coupler without valve, with Tap, Male BSPP Thread

Nickel-plated brass, NBR




DN	C		F	G	H
12	G1/2	2270 21 00	28	29	40.5

Flow = 2200 NI/min

2292 Universal Coupler Adaptor

Nickel-plated brass, NBR




DN			G	L
12		2292 12 00	29	40.5

Without shut-off

This adaptor provides interchangeability with numerous components (especially watering accessories).

2398 Universal Plug Adaptor

Nickel-plated brass, NBR




DN			G	L	L1	L2
12		2398 12 01	20	43	19	18.5

This adaptor provides interchangeability with numerous components (especially watering accessories).

2299 Water Pistol

Zamak, nickel-plated brass, NBR



DN			H	L
12		2299 12 01	140	126
12		2299 12 20		77.4

This pistol allows independent control of:

- the flow rate (trigger)
- type of jet (adjustable to a fine mist) by the adjustable nozzle