



SPFD 20 x 165 - 1 pc

SPEED FEED™ WOOD DRILL BITS

- Step up from flat bit in quality and performance - faster drilling, higher lifetime and less jamming!
- Dual cutting edges for fast and aggressive cut - up to 10 times faster drilling vs. flat boring bit.
- Tapered design for reduced chip clogging, less friction and less jamming even in tough applications - results in less breakages.
- Feed screw with coarse thread increases selffeeding in all types of wood - soft & hard, wet & treated.
- Polished and powder coated flute design for increased chip ejection, reduced clogging and higher selffeeding capability.



ø (inch)	¾"
ø (mm)	20
Article Number	4932479473, 48130068
Pack quantity	1
Shank reception	¼" Hex
Total length (mm)	165