

**AS1802 (1084G)**  
**SILCOTHERM 1 Part RTV silicone adhesive sealant paste non corrosive**

**Introduction**

**AS1802** is a non-corrosive, 1-part, room temperature vulcanising (RTV) silicone rubber. It is one of a new family of products called acetone cure sealants that are solvent free. It exhibits excellent primerless adhesion to many substrates. The product is cured rapidly in contact with atmospheric moisture to a tough rubber. It does not corrode copper or its alloys and exhibits excellent primerless adhesion when fully cured.

**Key Features**

- **Excellent thermal conductivity**
- **Non corrosive**
- **Fast skinning**
- **Low linear shrinkage**
- **Will meet the requirements of UL94V0**

**Use and Cure Information**

**How to Use**

**AS1802** is ready for use. If supplied in cartridges it can be applied using either manual or pneumatic dispensers. It can also be applied from bulk containers using conventional drum dispensing equipment.

**Application and Cure**

All surfaces to which the sealant is to be applied should be clean, dry and free from grease, dirt, and loose material. Priming of surfaces is not normally required. If AS1802 is being employed as an adhesive, it should be applied to one clean surface and the other clean surface brought into contact with it within 15 to 20 seconds. For optimum bond strength the thickness of the sealant joint is 1 to 2mm. Joints should be left undisturbed for at least 24 hours, but preferably longer to effect sufficient depth of cure. Full cure requires 7 days.

**Health and Safety** – Material Safety Data Sheets available on request

**Packages** - 310 ml cartridge and 25 kg pails. Please contact your regional sales manager for additional packaging options

**Storage and Shelf Life** – Expected to be 12 months in original, unopened containers when stored at <40°C

Property	Test Method	Value
<b>Uncured Product</b>		
Colour:		Grey
Appearance:		Grey Paste
Viscosity:	Brookfield	350000 mPa.s
Tack Free Time:		4 minutes *
3mm Cure Through:		<8 hours *
* measured at 23+/-2°C and 65% relative humidity.		

**Cured Elastomer**  
**(after 7 days cure at 23+/-2°C and 65% relative humidity)**

Tensile Strength:	BS903 Part A2	3.90 MPa
Elongation at Break:	BS903 Part A2	103 %
Hardness:	ASTM D 2240-95	67 Shore A
Specific Gravity:	BS 903 Part A1	2.11
Linear Shrinkage:		0.5 %
Thermal Conductivity:		2.30 W/mK
Coefficient of Thermal Expansion:		
Volumetric		493 ppm / °C
Linear		164 ppm / °C
Min. Service Temperature:		-50 °C
Max. Service Temperature:	AFS 1540B	220 °C

**Electrical Properties**

Volume Resistivity:	ASTM D-257	1x10 <sup>14</sup> Ω.cm
Dielectric Strength:	ASTM D-149	20 kV/mm
Dielectric Constant at 1MHz:	ASTM D-150	4.90
Dissipation Factor at 1MHz:	ASTM D-150	0.9x10 <sup>-3</sup>
Comparative Tracking Index (CTI)		
Expected to be >600 volts (PLC 0)		

**Adhesion Testing**

Overlap Shear Strength:	ASTM D 1002	kg/cm <sup>2</sup>
Copper		3.60
Aluminium		7.15
Stainless Steel 304		2.98

Customers are advised to carry out their own tests on clean, degreased substrates to ensure satisfactory adhesion is achieved.

Stress cracking can appear on some grades of polycarbonate. Customers are advised to carry out initial testing to ensure product compatibility.

All values are typical and should not be accepted as a specification.

**Revision Date: 01/09/2015**

The information and recommendations in this publication are to the best of our knowledge reliable. However nothing herein is to be construed as a warranty or representation. Users should make their own tests to determine the applicability of such information or the suitability of any products for their own particular purposes. Statements concerning the use of the products described herein are not to be construed as recommending the infringement of any patent and no liability for infringement arising out of any such use is to be assumed.