

Product data sheet

Subminiature connectors




Product description	M9 Male angled connector, Contacts: 7, 3.5-5.0 mm, unshielded, solder, IP67
Area	M9 IP67
Series	712
Part no.	99 0421 70 07


Illustration



Scale drawing



Contact arrangement (Plug-in side)



You can find the assembly instructions on the next page.

Technical data

General features

Part no.	99 0421 70 07
Connector design	Male angled connector
Version	Connector pin angled
Connector locking system	screw
Termination	solder
Degree of protection	IP67
Connection cross-section	max. 0.14 mm ² / AWG 26
Cable outlet	3.5-5.0 mm
Twistability	180° (2 coding options)
Temperature range from/to	-40 °C / 85 °C
Mechanical operation	> 500 Mating cycles
Weight (g)	8.81
Customs tariff number	85369010
Country of Origin	DE

Electrical parameters

Rated voltage	125 V
Rated impulse voltage	1500 V
Rated current	1.0 A
Insulation resistance	≥ 10 ⁸ Ω
Pollution degree	1
Overvoltage category	II
Insulating material group	III
EMC compliance	unshielded

Product data sheet

Subminiature connectors



Product description	M9 Male angled connector, Contacts: 7, 3.5-5.0 mm, unshielded, solder, IP67
Area	M9 IP67
Series	712
Part no.	99 0421 70 07

Material

Housing material	PA/CuZn (Nickel-plated brass)
Contact body material	PBT (UL94 V-0)
Contact material	CuZn (brass)
Contact plating	Au (gold)
Locking material	CuZn (brass)
REACH SVHC	CAS 7439-92-1 (Lead)
SCIP number	da35ec1e-3480-4466-ab8f-74b32e858c2f

Classifications

eCl@ss 11.1	27-44-01-02
ETIM 9.0	EC002635

Declarations of conformity

Low Voltage Directive	EN 60529:1991 EN 60204-1:2018
-----------------------	---------------------------------

Trade-Compliance

Copper (9903.78.01)	0.000221 kg
---------------------	-------------

Assembly instructions

1. Bead parts to cable.

2. Dismantle cable to 12 mm length.

3. Strip single wires (L = 3 mm).

4. Bead single wires through housing.
Mount seal and pinch ring, turn on pressing screw.

5. Solder single wires.

6. Screw housing to contact insert and tighten pressing screw.

angled housing
180° turnable

0,4 Nm

female insert

male insert

12

3 strip

dismantle

seal

pinch ring

pressing screw
 0,3-0,4 Nm

Date: 28.04.2026

Product description	M9 Male angled connector, Contacts: 7, 3.5-5.0 mm, unshielded, solder, IP67
Area	M9 IP67
Series	712
Part no.	99 0421 70 07

General Disclaim Notice

The connector must not be plugged or unplugged under load. Non-observance and improper use can result in personal injury.

The connectors have been developed for applications in plant engineering, control and electrical equipment construction. The user is responsible for checking whether the connectors can also be used in other areas of application.

To protect against unintentional opening of the connector, the thread between the housing and the connector head must be secured with a suitable cyanoacrylate adhesive when used in circuits with voltages dangerous to the touch. This does not apply to connectors used in SELV and PELV circuits according to IEC 61140 (EN 61140, VDE 0140-1).

Connectors which are used in circuits with voltages dangerous to the touch may only be installed and used by, or under the supervision of, persons with electrical engineering training, taking into account the applicable regulations and standards.

The user must take suitable safety precautions to ensure that the connector cannot be accidentally disconnected.

Plug connectors with enclosure protection IP67 and IP68 are not suitable for use under water. When used outdoors, the plug connectors must be protected separately against corrosion. For further information on the IP protection classes, please refer to the "Technical Information" download centre.

Please observe the pollution degree and the overvoltage category. For further information, please refer to the download center "Technical Information".