




Positive Lock | Positive Lock 187

TE Internal #: 173724-1

Quick Disconnect Receptacle, 20 – 14 AWG, .51 – 2.08 mm² Wire,
4.75 mm [.187 in] Tab Width, Straight, Brass, Pre-Tin Plating,
Positive Lock 187

[View on TE.com >](#)

Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **.51 – 2.08 mm²**

Mating Tab Width: **4.75 mm [.187 in]**

Mating Tab Thickness: **.51 mm [.02 in]**

Features

Product Type Features

Insertion Force	Low
-----------------	-----

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
Connection Capacity	Single

Electrical Characteristics

Voltage Rating	250 V
----------------	-------

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	4.75 mm[.187 in]
Mating Tab Thickness	.51 mm[.02 in]
Terminal Orientation	Straight
Contact Base Material	Brass
Terminal Plating Material	Pre-Tin
Crimp Type	F-Crimp



Barrel Type	Open
Termination Features	
Product Terminates To	Wire & Cable
Mechanical Attachment	
Wire Insulation Support	With
Dimensions	
Product Length	17.2 mm[.677 in]
Compatible Insulation Diameter Range	1.9 – 4.4 mm[.074 – .173 in]
Terminal Material Thickness	.3 mm[.012 in]
Wire Size	.51 – 2.08 mm²
Usage Conditions	
Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]
Packaging Features	
Packaging Quantity	6000
Packaging Method	Strip/Reel
Product Compliance	
For compliance documentation, visit the product page on TE.com>	
EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these



limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 2150058-2 OCEAN_2.0_Applicator-E-110F200F-REA	 TE Part # 2232342-1 187 PL EX FLAG REC. 22-16AWG PTBR	 TE Part # 1-172075-1 3 POS PL 187(4.8 MM) HOUSING NATURAL	 TE Part # 7-2150058-7 OCEAN_2.0_SPARE_PART_KIT-110F200F
 TE Part # 1743058-1 PL 187 REC 22-16 AWG 0.3 X 22.8 PTBR	 TE Part # 2150058-1 OCEAN_2.0_Applicator-E-110F200F-REM	 TE Part # 1743221-1 250 PL EX FLAG REC. 18-12AWG PTBR	 TE Part # 2013799-1 250 HSG. PL EX REC. BLACK

Also in the Series | Positive Lock 187

 Crimp Terminal Housings(85)	 Insertion & Extraction Tools(2)	 Insulation Boots & Sleeves(7)	 Quick Disconnects(57)
---------------------------------	-------------------------------------	-----------------------------------	---------------------------

Customers Also Bought



TE Part #2108743-1
POWER 2P DBL L/PRO NAT



TE Part #1376477-4
2.5MM PITCH SIGNAL MATE CONN




TE Part #3-293041-2
FASTIN FASTON 250 TAB 0.35-1.00
MM2 PTPBR




TE Part #170325-1
187 PL MKII REC. 20-16AWG PTBR




TE Part #174777-1
PL 110 REC 20-16 AWG 0.25 X 10.4
PTBR



TE Part #2-2005820-9
CLUSTER BLOCK 3P CLIP HSG(GWT)



TE Part #281622-2
MAG-MATE TAB STD SNPL



TE Part #2-2176422-5
TLRP 2512 3.0W R025 1% 25PPM 4K RL



TE Part #293230-2
RAST2.5 W2W Crimp-IDC 4pos Motor
Mnt



TE Part #173724-7
PL 187 REC 20-18 AWG 0.30 X 38.6
PTBR

Documents

Product Drawings

187 PL EX REC. 20-14AWG PTBR

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_173724-1_W.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_173724-1_W.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_173724-1_W.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications



Application Specification

English

Instruction Sheets

Instruction Sheet (non U.S.)

English

POSITIVE LOCK EX CONTACT

English

Agency Approvals

UL Report

English

UL Report

English