

Interface module - UMK- EC38/38-XOR - 2976297

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)




VARIOFACE module, for ELCO connector, for mounting on NS 35/7.5 or NS 32, with pin strip 8016 right, no. of positions 38

The illustration shows the left-hand version



Key commercial data

| | |
|--------------------------------------|---|
| Packing unit | 1 pc |
| GTIN |  4 017918 089320 |
| Weight per Piece (excluding packing) | 195.68 g |
| Custom tariff number | 85369010 |
| Country of origin | Germany |

Technical data

Dimensions

| | |
|--------|----------|
| Width | 101.5 mm |
| Height | 77 mm |
| Depth | 58.5 mm |

Ambient conditions

| | |
|---------------------------------|------------------|
| Ambient temperature (operation) | -20 °C ... 40 °C |
|---------------------------------|------------------|

General

| | |
|---|-----------|
| Nominal voltage U_N | 25 V AC |
| | 60 V DC |
| Max. current carrying capacity per branch | 2 A |
| Max. total current of all branches | 76 A |
| Number of positions | 38 |
| Mounting position | any |
| Standards/regulations | IEC 60664 |

Interface module - UMK- EC38/38-XOR - 2976297

Technical data

General

| | |
|--------------------------|--------------|
| | DIN EN 50178 |
| | IEC 62103 |
| Pollution degree | 2 |
| Surge voltage category | II |
| Rated surge voltage | 0.8 kV |
| Rated insulation voltage | 85 V |

Connection data for connection 1

| | |
|--|---------------------|
| Connection name | PCB connection |
| Connection in acc. with standard | IEC / EN |
| Connection method | Screw connection |
| Conductor cross section solid min. | 0.2 mm ² |
| Conductor cross section solid max. | 4 mm ² |
| Conductor cross section stranded min. | 0.2 mm ² |
| Conductor cross section stranded max. | 2.5 mm ² |
| Conductor cross section AWG/kcmil min. | 24 |
| Conductor cross section AWG/kcmil max | 12 |
| Stripping length | 8 mm |
| Screw thread | M3 |

Connection data for connection 2

| | |
|-----------------------|-----------------|
| Connection name | ELCO connection |
| Number of connections | 1 |
| Connection method | ELCO connector |
| Number of positions | 38 |

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 27250313 |
| eCl@ss 4.1 | 27250313 |
| eCl@ss 5.0 | 27250313 |
| eCl@ss 5.1 | 27250313 |
| eCl@ss 6.0 | 27242608 |
| eCl@ss 7.0 | 27141152 |
| eCl@ss 8.0 | 27141152 |

ETIM

| | |
|----------|----------|
| ETIM 2.0 | EC001434 |
| ETIM 3.0 | EC001604 |
| ETIM 4.0 | EC001604 |
| ETIM 5.0 | EC002780 |

Interface module - UMK- EC38/38-XOR - 2976297

Classifications

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 30211824 |
| UNSPSC 7.0901 | 39121421 |
| UNSPSC 11 | 39121421 |
| UNSPSC 12.01 | 39121421 |
| UNSPSC 13.2 | 39121421 |

Approvals

Approvals


Approvals

GOST

Ex Approvals

Approvals submitted

Approval details



Drawings

Dimensioned drawing

