

## Passive module - VIP-2/PT/FLK50/PLC - 2903803

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



VARIOFACE interface module, with push-in connection, for 32 channels



### Key commercial data

Packing unit	1 pc
GTIN	
Weight per Piece (excluding packing)	224.1 g
Custom tariff number	85369010
Country of origin	United States
Note	Made to Order (non-returnable)

### Technical data

#### Dimensions

Width	107.9 mm
Height	72.1 mm
Depth	56 mm

#### Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

#### General

Max. permissible operating voltage	60 V AC/DC
Max. perm. current (per branch)	1 A
Max. permissible current (separate power supply)	2 A (per byte)
Number of positions	50
Status display	No
Mounting position	any

# Passive module - VIP-2/PT/FLK50/PLC - 2903803

## Technical data

### General

Standards/regulations	IEC 60664
	DIN EN 50178
	IEC 62103
Rated surge voltage	0.6 kV
Pollution degree	2
Surge voltage category	II

### Connection data for connection 1

Connection name	Field level
Connection method	Push-in connection
Conductor cross section solid min.	0.14 mm <sup>2</sup>
Conductor cross section solid max.	2.5 mm <sup>2</sup>
Conductor cross section stranded min.	0.14 mm <sup>2</sup>
Conductor cross section stranded max.	2.5 mm <sup>2</sup>
Conductor cross section AWG/kcmil min.	26
Conductor cross section AWG/kcmil max	14
Stripping length	8 mm

### Connection data for connection 2

Connection name	Controller level
Number of connections	1
Connection method	IDC/FLK pin strip (2.54 mm)
Number of positions	50

### Supported controller

Controller	ALLEN-BRADLEY ControlLogix
- suitable I/O card	1756-IA16I
	1756-IB16D
	1756-IB16I
	1756-IB32
	1756-IH16I
	1756-OB32
	1756-IF8
	1756-IF16
	1756-HSC
	1756-M02AE
	1756-IF8H
Controller	ALLEN-BRADLEY PLC 5
- suitable I/O card	1771 IBN
	1771 OBN
Controller	GE-FANUC RX3i
- suitable I/O card	IC694MDL754

## Passive module - VIP-2/PT/FLK50/PLC - 2903803

### Technical data

#### Supported controller

	IC694MDL660
Controller	HONEYWELL PlantScape
- suitable I/O card	TC-IDD 321
	TC-ODD 321
Controller	MITSUBISHI MELSEC Q
- suitable I/O card	QX41
	QX41-S1
	QX42
	QX42-S1
	QX71
	QX72
	QY41P
	QY42P
	QY71
	QH42P
	QX82
	QX82-S1
Controller	MITSUBISHI MELSEC L
- suitable I/O card	LX41C4
	LX42C4
	LY41NT1P
	LY42NT1P
	LY41PT1P
	LY42PT1P

### Classifications

#### eCl@ss

eCl@ss 4.0	27250313
eCl@ss 4.1	27250313
eCl@ss 5.0	27250313
eCl@ss 5.1	27250313
eCl@ss 6.0	27242608
eCl@ss 7.0	27141152
eCl@ss 8.0	27141152

#### ETIM

ETIM 2.0	EC001434
ETIM 3.0	EC001604
ETIM 4.0	EC001604
ETIM 5.0	EC002780

# Passive module - VIP-2/PT/FLK50/PLC - 2903803

## Classifications

### UNSPSC

UNSPSC 6.01	30211824
UNSPSC 7.0901	39121421
UNSPSC 11	39121421
UNSPSC 12.01	39121421
UNSPSC 13.2	39121421

## Approvals

### Approvals

#### Approvals

CSA / UL Recognized / cUL Recognized / EAC / cULus Recognized

#### Ex Approvals

#### Approvals submitted

## Approval details

CSA	
mm <sup>2</sup> /AWG/kcmil	26-14
Nominal current IN	1 A
Nominal voltage UN	125 V

UL Recognized	
mm <sup>2</sup> /AWG/kcmil	26-14
Nominal current IN	1 A
Nominal voltage UN	125 V

# Passive module - VIP-2/PT/FLK50/PLC - 2903803

## Approvals

cUL Recognized	
mm <sup>2</sup> /AWG/kcmil	26-14
Nominal current I <sub>N</sub>	1 A
Nominal voltage U <sub>N</sub>	125 V

EAC
-----

cULus Recognized
------------------

## Accessories

### Accessories

#### Printing system

Printer - BLUEMARK X1 - 5147777



Printers with UV technology for printing plastic labels in UniCard format.

### System cable

Cable - FLK 50/EZ-DR/ 50/KONFEK - 2289065



Round cable set, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 0.5 m

Cable - FLK 50/EZ-DR/ 100/KONFEK - 2289078



Round cable sets, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 1 m

## Passive module - VIP-2/PT/FLK50/PLC - 2903803

### Accessories

Cable - FLK 50/EZ-DR/ 150/KONFEK - 2289081



Round cable set, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 1.5 m

---

Cable - FLK 50/EZ-DR/ 200/KONFEK - 2289094



Round cable sets, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 2 m

---

Cable - FLK 50/EZ-DR/ 250/KONFEK - 2289104



Round cable set, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 2.5 m

---

Cable - FLK 50/EZ-DR/ 300/KONFEK - 2289117



Round cable sets, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 3 m

---

Cable - FLK 50/EZ-DR/ 350/KONFEK - 2289120



Round cable set, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 3.5 m

---

## Passive module - VIP-2/PT/FLK50/PLC - 2903803

### Accessories

Cable - FLK 50/EZ-DR/ 400/KONFEK - 2289133



Round cable set, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 4 m

---

Cable - FLK 50/EZ-DR/ 450/KONFEK - 2289573



Round cable set, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 4,5 m

---

Cable - FLK 50/EZ-DR/ 500/KONFEK - 2289586



Round cable set, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 5 m

---

Cable - FLK 50/EZ-DR/ 550/KONFEK - 2289599



Round cable set, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 5,5 m

---

Cable - FLK 50/EZ-DR/ 600/KONFEK - 2289609



Round cable set, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 6 m

---

## Passive module - VIP-2/PT/FLK50/PLC - 2903803

### Accessories

Cable - FLK 50/EZ-DR/ 650/KONFEK - 2289612



Round cable set, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 6.5 m

---

Cable - FLK 50/EZ-DR/ 700/KONFEK - 2289625



Round cable set, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 7 m

---

Cable - FLK 50/EZ-DR/ 750/KONFEK - 2289638



Round cable set, with two 50-pos. female connectors (1:1 connection), for connecting 32 channels, cable length: 7.5 m

---

Cable - FLK 50/EZ-DR/ 800/KONFEK - 2289641



Round cable sets, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 8 m

---

Cable - FLK 50/EZ-DR/ 850/KONFEK - 2289654



Round cable set, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 8.5 m

---



## Passive module - VIP-2/PT/FLK50/PLC - 2903803

### Accessories

Cable - FLK 50/EZ-DR/ 900/KONFEK - 2289667



Round cable set, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 9 m

---

Cable - FLK 50/EZ-DR/ 950/KONFEK - 2289670



Round cable set, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 9.5 m

---

Cable - FLK 50/EZ-DR/1000/KONFEK - 2289683



Round cable set, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 10 m

---

Cable - FLK EZ-DR.../.../... - 2295059



Round cable, with preassembly, not shielded, variable cable length

---

Cable - FLK 50/EZ-DR/ 50/KONFEK/S - 2299097



Round shielded cable set, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 0.5 m

---

## Passive module - VIP-2/PT/FLK50/PLC - 2903803

### Accessories

Cable - FLK 50/EZ-DR/ 100/KONFEK/S - 2299107



Round shielded cable set, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 1 m

---

Cable - FLK 50/EZ-DR/ 150/KONFEK/S - 2299110



Round shielded cable set, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 1.5 m

---

Cable - FLK 50/EZ-DR/ 200/KONFEK/S - 2299123



Round shielded cable set, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 2 m

---

Cable - FLK 50/EZ-DR/ 300/KONFEK/S - 2299136



Round shielded cable set, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 3 m

---

Cable - FLK 50/EZ-DR/ 400/KONFEK/S - 2299149



Round shielded cable set, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 4 m

---

## Passive module - VIP-2/PT/FLK50/PLC - 2903803

### Accessories

Cable - FLK 50/EZ-DR/ 600/KONFEK/S - 2299152



Round shielded cable set, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 6 m

---

Cable - FLK 50/EZ-DR/ 800/KONFEK/S - 2299165



Round shielded cable set, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 8 m

---

Cable - FLK 50/EZ-DR/1000/KONFEK/S - 2299178



Round shielded cable set, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 10 m

---

Cable - FLK EZ-DR-S.../.../... - 2295046



Round cable, with preassembly, shielded, variable cable length

---

Cable - CABLE-FLK50/0,14/HF/ 0,5M - 2314134



Assembled halogen-free round cable, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels. Halogen-free refers exclusively to the 50-pos. cable. Length of cable: 0.55 yd

---

## Passive module - VIP-2/PT/FLK50/PLC - 2903803

### Accessories

Cable - CABLE-FLK50/0,14/HF/ 1,0M - 2314147



Assembled halogen-free round cable, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels. Halogen-free refers exclusively to the 50-pos. cable. Length of cable: 1 m

Cable - CABLE-FLK50/0,14/HF/ 1,5M - 2314150



Assembled halogen-free round cable, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels. Halogen-free refers exclusively to the 50-pos. cable. Length of cable: 1.64 yd

Cable - CABLE-FLK50/0,14/HF/ 2,0M - 2314163



Assembled halogen-free round cable, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels. Halogen-free refers exclusively to the 50-pos. cable. Length of cable: 2.19 yd

Cable - CABLE-FLK50/0,14/HF/ 2,5M - 2314176



Assembled halogen-free round cable, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels. Halogen-free refers exclusively to the 50-pos. cable. Length of cable: 2.73 yd

Cable - CABLE-FLK50/0,14/HF/ 5,0M - 2314202



Assembled halogen-free round cable, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels. Halogen-free refers exclusively to the 50-pos. cable. Length of cable: 5 m

## Passive module - VIP-2/PT/FLK50/PLC - 2903803

### Accessories

Cable - CABLE-FLK50/0,14/HF/ 6,0M - 2314215



Assembled halogen-free round cable, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels. Halogen-free refers exclusively to the 50-pos. cable. Length of cable: 6 m

Cable - CABLE-FLK50/0,14/HF/ 7,0M - 2314228



Assembled halogen-free round cable, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels. Halogen-free refers exclusively to the 50-pos. cable. Length of cable: 7 m

Cable - CABLE-FLK50/0,14/HF/ 8,0M - 2314231



Assembled halogen-free round cable, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels. Halogen-free refers exclusively to the 50-pos. cable. Length of cable: 8 m

Cable - CABLE-FLK50-0,14-HF/... - 2314257



Assembled halogen-free round cable, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels. Halogen-free refers exclusively to the 50-pos. cable. Length of cable: Variable

### Terminal marking

Marker for terminal blocks - UC-TM 4 - 0818111



Marker for terminal blocks, Sheet, white, unlabeled, can be labeled with: BLUEMARK CLED, BLUEMARK LED, Plotter, Mounting type: Snap into tall marker groove, for terminal block width: 4.2 mm, Lettering field: 3.6 x 10.5 mm

# Passive module - VIP-2/PT/FLK50/PLC - 2903803

## Accessories

Marker for terminal blocks - UC-TM 6 - 0818085



Marker for terminal blocks, Sheet, white, unlabeled, can be labeled with: BLUEMARK CLED, BLUEMARK LED, Plotter, Mounting type: Snap into tall marker groove, for terminal block width: 6.2 mm, Lettering field: 5.6 x 10.5 mm

Zack marker strip - ZB 5,08:UNBEDRUCKT - 0809793



Zack marker strip, Strip, white, unlabeled, can be labeled with: Plotter, Mounting type: Snap into tall marker groove, for terminal block width: 5.08 mm, Lettering field: 4.98 x 10.5 mm

Zack marker strip - ZB 22:UNBEDRUCKT - 0811862



Zack marker strip, Strip, white, unlabeled, can be labeled with: Plotter, Mounting type: Snap into tall marker groove, for terminal block width: 22 mm, Lettering field: 10.5 x 21.8 mm

## Drawings

Circuit diagram

