



Product designation

Product type designation

Auxiliary supply voltage

Number of inputs

Number of outputs

Max I/O number

Micro PLC - Base module

LRD12RA024

24VAC

Nr. 8 digital

Nr. 4 relay

12 (8 inputs + 4 outputs) up to 36 with LRE modules

Power supply

Rated auxil. supply voltage		24VAC
Operating voltage range		20.4...28.8VAC
Rated frequency	Hz	50/60
Operating frequency range	Hz	47...63
Average current consumption	mA	290
Power consumption Max	W	7

Digital inputs

Number of digital input	Nr.	8
Rated voltage	V	24VAC (50/60Hz)
Input signals	State 0 (OFF) State 1 (ON)	<6VAC >14VAC

Response time

0 to 1 (OFF-ON)	90ms
1 to 0 (ON-OFF)	90ms

Digital outputs

Number of digital output	Nr.	4
type		Relay

System resources

Display	LCD display, 4 lines x 16 characters
---------	--------------------------------------

Connections

Terminals type	Screw
Tightening torque for terminals	max Nm 0.6 Max lbft 0.4

Conductor section

AWG/Kcmil

min	26
max	14

IEC

min	mm ² 0.14
max	mm ² 2.5

Ambient conditions

Temperature

Operating temperature

min	°C	-20
max	°C	+55

Storage temperature

min	°C	-40
max	°C	+70

Relative humidity

%	20...90% without condensation
---	-------------------------------

Housing

Mounting

35mm DIN rail or screw fixing (M4x20mm)

Degree of protection

IP20


Dimensions (W x H x D)

mm 72 x 106 x 59.6


Weight

g 250

Dimensions



Wiring diagrams



Certifications and compliance

Compliance

CSA C22.2 n° 142
IEC/EN 61131-2
UL508

Certificates

cULus

EAC

ETIM classification

ETIM 8.0

EC001417 -
Logic module