

FEATURES

- **Conical tip shape:** Allows for precise soldering in tight spaces, enhancing accuracy.
- **0.4 mm tip width:** Suitable for detailed work on small components, improving efficiency.
- **9.5 mm tip length:** Provides optimal reach for various soldering applications, increasing versatility.
- **0° tip angle:** Ensures consistent contact with surfaces, promoting uniform heat distribution.
- **ANSI-ESD S20.20:2021 compliance:** Meets electrostatic discharge safety standards, protecting sensitive components.
- **REACH and RoHS compliant:** Environmentally friendly, adhering to key safety and environmental regulations.

RS PRO Soldering Iron Tip, Conical, 0.4 mm Width

RS Stock No: 631-087



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO soldering iron tip is designed for precision soldering tasks, providing excellent performance when used with the 0631071 Soldering Station. Its conical shape and fine tip width make it ideal for intricate electronic work, ensuring accuracy and reliability.

General Specifications

For Use With	0631071 Soldering Station
Product Type	Soldering Iron Tip
Tip Angle	0 °
Tip Series	T80
Tip Shape	Conical

Approvals

Standards/Approvals	ANSI-ESD S20.20:2021, REACH, RoHS
---------------------	-----------------------------------

Mechanical Specifications

Tip Length	9.5 mm
Tip Width	0.4 mm

