




7F.20-4400
7F.30-4400

7F.02
7F.03


7F.2x.x.xxx.4400 7F.2x.x.xxx.4400.0 7F.3x.x.xxx.4400	
	U _N 110...120 V AC (50/60 Hz) (8.120) U _N 230...240 V AC (50/60 Hz) (8.230)
	P _N 120 V AC (50/60 Hz) 72/120 W P _N 230 V AC (50/60 Hz) 69/112 W
OUT	m ³ /h (50/60Hz) 400/445
	m ³ /h (50/60Hz) 270/300
	dB (A) 72 (AC)
	(-15...+55)°C (-30...+55)°C only for 7F.3x
IP54 / Type 12 -> 7F.2x IP54 / Type 3R -> 7F.3x	
 For Use on a Flat Surface of a Type 1, 12 Enclosure (For type 7F.2x) For Use on a Flat Surface of a Type 1, 3R Enclosure (For type 7F.3x) Use copper conductor only, 90°C min Conductor size 14-18 AWG Surrounding air temperature 55°C	

1




0.75...2.5 mm²

18...14 AWG




2



7F.2x
7F.3x





7F.02
7F.03



3



4



ENGLISH

FOR INDOOR USE:

7F.20 FILTER FAN

7F.21 FILTER FAN WITH REVERSE FLOW FILTER

FOR OUTDOOR USE:

7F.30 FILTER FAN

7F.31 FILTER FAN WITH REVERSE FLOW FILTER

1

WIRING DIAGRAM AC

2

OUTLINE DRAWING (mm)

7F.2x/3x Fan

7F.02/03 Grid

3

GRID OPENING - FILTER REPLACEMENT

Spare filters: Fan 07F.46

Exhaust 07F.45

Filter mat class

EU3 according to DIN 24185, filtering degree (80...90)%.

Filter material

Synthetic fibre with progressive construction, temperature resistant to 100°C, self extinguishing, Class F1 (DIN 53438).

4

MOUNTING (example)

The installation with the only clips is optimized for 1.5 mm thick sheets.

It is also possible with thicknesses from 2.5 mm.

Fixing with screws (supplied) is recommended.

Tightening torque 0.3 Nm.

NOTE

For indoor use

7F.2x.x.xxx.4400	Fan	Grey Color	RAL 7035
------------------	-----	------------	----------

7F.2x.x.xxx.4400.0	Fan	Black Color	RAL 9004
--------------------	-----	-------------	----------

7F.02.0.000.4000	Grid	Grey Color	RAL 7035
------------------	------	------------	----------

7F.02.0.000.4000.0	Grid	Black Color	RAL 9004
--------------------	------	-------------	----------

For outdoor use

7F.3x.x.xxx.4400	Fan	Grey Color	RAL 7000
------------------	-----	------------	----------

7F.03.0.000.4000	Grid	Grey Color	RAL 7000
------------------	------	------------	----------

