



Technical data


NUP207EAT2XC3U

Single row cylindrical roller bearings

Single row cylindrical roller bearing, locating, separable, polyamide cage


ULTAGE®

VISUAL (S)



NUP207EAT2XC3U



Single row cylindrical roller bearings



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

NUP207EAT2XC3U
Single row cylindrical roller bearings



PRODUCT DEFINITION

Brand	NTN
d - Internal diameter	35 mm
D - External diameter	72 mm
B - Bearing/Inner ring width	17 mm



PRODUCT DEFINITION

E - Upper roller diameter	64 mm
F - Under roller diameter	44 mm
d1 - IR flange outer diameter	48 mm
rNs - Min fillet radius	0,6 mm
rs - Min fillet radius	1,1 mm
Radial clearance class	C3

PRODUCT PERFORMANCE

C - Dynamic load	59500000 mN
C0 - Static load	50000000 mN
Cu - Fatigue limit load	6100000 mN
N lim - Oil lubrication limit speed	79200 °/s
N lim - Grease lubrication limit speed	57000 °/s
Tmin - Min operating temperature	253,15 °K
Tmax - Max operating temperature	393,15 °K

ABUTMENT

da min - Min shoulder diameter IR	39 mm
Da max - Max shoulder diameter OR	65,5 mm
Db min - Small face shoulder min diameter	65,5 mm
ra max - Max fillet radius	1 mm
r1a - Max fillet radius	0,6 mm



INDUSTRY CALCUL FACTORS

Equivalent dynamic radial load

$$P = Fr$$

Equivalent static radial load

$$P_0 = Fr$$



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15