



**RASE35-XL-N**

Plummer block housing unit

Plummer block housing units RASE, cast iron housing, radial insert ball bearing with eccentric locking collar, R seals

X-life

Technical information



Your current product variant

|          |    |                                                   |
|----------|----|---------------------------------------------------|
| Material | GG | Grey cast iron                                    |
| Groove   | N  | Cast iron housing with undercut slot for end caps |

Main Dimensions & Performance Data

|     |          |               |
|-----|----------|---------------|
| d   | 35 mm    | Bore diameter |
| L   | 163 mm   | Length total  |
| H 2 | 93 mm    | Height        |
| ≈m  | 1.646 kg | Weight        |

Mounting dimensions

|     |        |                      |
|-----|--------|----------------------|
| J   | 126 mm | Distance fixing bore |
| N   | 14 mm  | Width (slot)         |
| N 1 | 21 mm  | Length (slot)        |



Dimensions

|                |         |                                       |
|----------------|---------|---------------------------------------|
| H              | 47.6 mm | Distance shaft axis                   |
| A              | 45 mm   | Width (base)                          |
| A <sub>1</sub> | 27 mm   | Width (head)                          |
| H <sub>1</sub> | 19 mm   | Heigth (base)                         |
| B <sub>1</sub> | 51.3 mm | Locking collar total width            |
| S <sub>1</sub> | 32.5 mm | Distance of raceway to locking collar |
| Q              | M6      | Connection thread for lubrication     |

Additional information

|               |                     |
|---------------|---------------------|
| ASE07         | Housing             |
| GE35-XL-KRR-B | Bearing designation |
| KASK07        | Protecting cap      |

Temperature range

|                  |        |                            |
|------------------|--------|----------------------------|
| T <sub>min</sub> | -20 °C | Operating temperature min. |
| T <sub>max</sub> | 120 °C | Operating temperature max. |