



Main

Range	New Unica
Product or component type	Socket-outlet
Aesthetic name	Unica Studio
Device presentation	Complete product
Device mounting	Flush
Socket number	2
Outlet poles configuration	2P + E
Outlet standard	CEE 7/3
Outlet standard deviation	Schuko
Outlet standard description	Side earth
Rated current	16 A

Complementary





Device application	Power supply
Cover type	With shutter
[Ue] rated operational voltage	250 V
Network type	AC
Network frequency	50/60 Hz
Fixing mode	Screws
Colour tint	Anthracite (RAL 7021)
Connections - terminals	Screw terminals
Cable cross section	0...2.5 Mm ² cable(s), 2 - cable stiffness: flexible 0...2.5 mm ² cable(s), 2 - cable stiffness: rigid
Minimum load breaking capacity	100 operations 1.25 In and 1.1 Un, cos phi = 0.6
Electrical durability	10000 cycles, cos phi = 0.8
Insulation resistance	> 5 MOhm at 500 V
Dielectric strength	2000 V
Material	PC: mechanism cover
Surface finish	Painted
Quantity per set	Set of 1 flow-pack
Standards	IEC 60884-1 UNE 20315-1-1 UNE 20315-1-2 DIN VDE 0620-1
Product certifications	AENOR[RETURN]EAC
Embedding depth	24 mm
Depth	47 mm
Width	85 mm
Height	125 mm
Net weight	0.099 kg

Surface treatment	Painted
Resistance to chemical agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

Environment

Ambient air temperature for operation	-5...35 °C
Ambient air temperature for storage	-5...50 °C
IK degree of protection	IK04
IP degree of protection	IP21D
Environmental characteristic	Acetone Bleach UV resistant Petrol Oil Alcohol Window-cleaning fluid Liquid soap

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
Sustainable packaging	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins