

Enamelled copper wire on mini bobbin
CUL 500/0,63



Advantages

Insulating varnish basis min. polyurethane, mod. current loading

Degree 1

TJ min. 155 °C

Solderable

Applications

Enamelled copper wire for the production of coils and winding and for general laboratory needs.

Approvals



Enamelled copper wire on mini bobbin **CUL 500/0,63**

Type

CUL 500/0,63

Type

CUL 500/0,63



Electrical data



Mechanical data

Operating data

current car. cap. 1.00 A

Environment

Heat resistance 155 °C (CL.F)

insulating varnish min. Polyurethan, mod.

Tin-plate >350 °C

Measures and weights

Wire diameter 0.63 mm

Weight 0.50 kg

Length m (min.) 140

Subjects to change.