


KEMET Part Number: ALT22A681DB200 **Not for New Design**
(A663HG681M200A)

ALT22, Aluminum Electrolytic, 680 uF, 20%, 200 VDC, -40/+85°C



General Information	
Supplier:	KEMET
Series:	ALT22
Dielectric:	Aluminum Electrolytic
Description:	Solder Tag, Aluminum Electrolytic
Features:	Solder Tag
RoHS:	Yes
Lead:	2 Flying Leads Solder Tags
AEC-Q200:	No
Notes:	Dimensions D And L Include Slewing

Dimensions	
D	40mm +/-1mm
L	45mm +/-2mm
S	10mm +/-0.1mm
LL	10mm +/-0.5mm

Packaging Specifications	
Weight:	80 g
Slewing:	Yes
Packaging:	Bulk, Bag

Specifications	
Capacitance:	680 uF
Capacitance Tolerance:	20%
Voltage DC:	200 VDC, 230 VDC (Surge)
Temperature Range:	-40/+85°C
Rated Temperature:	85°C
Life:	26000 Hrs
Leakage Current:	816 uA (5min 20°C)