



DCG412NT

18V XR Li-Ion Grinder - Bare Unit

Selling Proposition

- Steel cut spiral bevel gears provide highest level of durability and low vibration, increasing user productivity
- Low profile jam pot gear case improves gear durability and ergonomics
- Intelligent trigger & lock-off switch for enhanced work safety & control
- Keyless guard for enhanced application versatility
- Two position side handle offers greater comfort and control
- Quick change wheel release allows quick and easy wheel removal

Standard Equipment

- 2 position side handle
- Keyless protective guard
- Blade wrench
- TSTAK II heavy-duty kitbox
- Battery and charger sold separately

Warranty Specifications

- DEWALT 3 year European PT Guarantee (subject to registration)

Specifications	
Power Input	
No Load Speed	7000 rpm
Max. Disc Diameter	125 mm
Spindle Thread	M14
Weight	2.2 kg
Length	400 mm
Height	125 mm
Hand/Arm Vibration - Grinding	6.0 m/s ²