

## D SUB HD FE STR 44P PL3



Image is for illustration purposes only. Please refer to product description.

Part number	09 56 351 7500
Specification	D SUB HD FE STR 44P PL3
HARTING eCatalogue	<a href="https://harting.com/09563517500">https://harting.com/09563517500</a>

### Identification

Category	Connectors
Series	D-Sub
Identification	High Density
Element	Connector
Description of the contact	Stamped Straight

### Version

Termination method	Wave soldering termination
Gender	Female
Size	D-Sub 3
Number of contacts	44
Locking type	Fixing flange with feed through hole $\varnothing$ 3.1 mm

### Technical characteristics

Distance between rows	1.98 mm
Contact spacing (termination side)	2.29 mm
Rated current	2 A
Clearance distance	$\geq 1$ mm
Creepage distance	$\geq 1$ mm
Insulation resistance	$> 5 \times 10^9 \Omega$
Contact resistance	$< 20$ m $\Omega$
Limiting temperature	-40 ... +85 °C



Pushing Performance  
Since 1945

## Technical characteristics

Performance level	3
Mating cycles	≥50
Test voltage $U_{r.m.s.}$	1 kV
Isolation group	IIIa ( $175 \leq CTI < 400$ )
PCB thickness	1.6 mm
Installation height	4.1 mm
Hot plugging	No

## Material properties

Material (insert)	Thermoplastic resin, glass-fibre filled (PBTP) Shell: steel, nickel plated
Colour (insert)	Black
Material (contacts)	Copper alloy
Surface (contacts)	Noble metal over Ni Mating side Sn over Ni Termination side
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	ecef7555-f643-4ceb-a337-fc54762297f1
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R26

## Specifications and approvals

Specifications	DIN 41652
----------------	-----------



**Pushing Performance**  
Since 1945

## Commercial data

Packaging size	100
Net weight	12.68 g
Country of origin	China
European customs tariff number	85366990
GTIN	5713140071773
eCl@ss	27440214 D-Sub coupler
ETIM	EC001136
UNSPSC 24.0	39121469