


IN5280



Inductive dual sensor for valve actuators

IND3004-BPKG/US-100-KPS/A2



Product characteristics

Electrical design	PNP
Output function	normally open
Sensing range [mm]	4
Housing	rectangular
Dimensions [mm]	26 x 40 x 47.5

Electrical data

Operating voltage [V]	10...36 DC
Current consumption [mA]	15; (36 V)
Protection class	II
Reverse polarity protection	yes

Outputs

Electrical design	PNP
Output function	normally open
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	250
Switching frequency DC [Hz]	1300
Short-circuit protection	yes
Type of short-circuit protection	pulsed
Overload protection	yes



Inductive dual sensor for valve actuators

IND3004-BPKG/US-100-KPS/A2

Detection zone		
Sensing range	[mm]	4
Real sensing range Sr	[mm]	4 ± 10 %
Operating distance	[mm]	0...3.25
Accuracy / deviations		
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminium: 0.3 / copper: 0.2
Hysteresis	[% of Sr]	1...15
Switch point drift	[% of Sr]	-10...10
Operating conditions		
Ambient temperature	[°C]	-25...80
Protection		IP 67
Tests / approvals		
EMC	EN 60947-5-2	
	EN 55011	class B
MTTF	[years]	1883
Mechanical data		
Weight	[g]	56
Housing		rectangular
Mounting		non-flush mountable
Dimensions	[mm]	26 x 40 x 47.5
Materials		housing: PBT
Displays / operating elements		
Display	switching status	1 x LED, yellow
Remarks		
Pack quantity		1 pcs.
Electrical connection - plug		
Connector: 1 x M12; coding: A; Moulded body: stainless steel (303/1.4305)		
		



Inductive dual sensor for valve actuators

IND3004-BPKG/US-100-KPS/A2

Connection

