




FAG

6240-M-C3

Deep groove ball bearing

Deep groove ball bearing 62...-M, single row, solid brass cage

Technical information



Your current product variant

|                                  |              |                                          |
|----------------------------------|--------------|------------------------------------------|
| Sealing                          | Without      | Not sealed                               |
| Cage                             | M            | Solid brass cage, rolling element guided |
| Tolerance class                  | PN           | Normal (PN)                              |
| Dimensional / heat stabilization | S1           | Rings dimensional stabilized up to 200°  |
| Lubricant                        | Without      | Bearing not greased                      |
| Radial internal clearance        | C3 (Group 3) | Internal clearance larger than CN        |
| Bore type                        | Z            | Cylindrical                              |

Main Dimensions & Performance Data

|                 |             |                                   |
|-----------------|-------------|-----------------------------------|
| d               | 200 mm      | Bore diameter                     |
| D               | 360 mm      | Outside diameter                  |
| B               | 58 mm       | Width                             |
| C <sub>r</sub>  | 270,000 N   | Basic dynamic load rating, radial |
| C <sub>0r</sub> | 310,000 N   | Basic static load rating, radial  |
| C <sub>ur</sub> | 12,800 N    | Fatigue load limit, radial        |
| n <sub>G</sub>  | 3,200 1/min | Limiting speed                    |
| n <sub>gr</sub> | 2,430 1/min | Reference speed                   |
| ≈m              | 26.291 kg   | Weight                            |



Mounting dimensions

|         |        |                                      |
|---------|--------|--------------------------------------|
| d a min | 217 mm | Minimum diameter shaft shoulder      |
| D a max | 343 mm | Maximum diameter of housing shoulder |
| r a max | 3 mm   | Maximum fillet radius                |

Dimensions

|       |           |                              |
|-------|-----------|------------------------------|
| r min | 4 mm      | Minimum chamfer dimension    |
| D 1   | 306.45 mm | Shoulder diameter outer ring |
| d 1   | 254.9 mm  | Shoulder diameter inner ring |

Temperature range

|       |        |                            |
|-------|--------|----------------------------|
| T min | -30 °C | Operating temperature min. |
| T max | 200 °C | Operating temperature max. |

Calculation factors

|     |      |                    |
|-----|------|--------------------|
| f 0 | 15.2 | Calculation factor |
|-----|------|--------------------|

Characteristics

|                                                                                     |                              |
|-------------------------------------------------------------------------------------|------------------------------|
|  | Radial load                  |
|  | Axial load in one direction  |
|  | Axial load in two directions |
|  | Grease Lubrication           |
|  | Oil Lubrication              |
|  | Not sealed                   |
|  | Large bearing                |