



Wire & Cable > Wire & Cable Accessories > Cable Ties



Cable Tie Style: **Standard**
Packaging Method: **Bag**
Tensile Strength: **82 Newton**
Product Length: **200 mm [7.9 in]**

Features

Product Type Features

Cable Tie Style	Standard
Tensile Strength	82 Newton

Body Features

Primary Product Color	Natural
Primary Product Material	Polyamide 6.6 GF

Dimensions

Compatible Cable Bundle Diameter Range	52 mm[2.04 in]
Product Length	200 mm[7.9 in]
Product Width	2.6 mm[.102 in]
Product Thickness	1 mm[.039 in]

Packaging Features

Packaging Method	Bag
Packaging Quantity	1000

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold



EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JAN 2025 (247)
Candidate List Declared Against: JUNE 2024 (241)
Does not contain REACH SVHC

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts

 TE Part # EC6492-000 13611438	 TE Part # EC6457-000 13611403	 TE Part # 823954-000 CM-SCE-TP-2.5K-1/4-4H-9	 TE Part # 0628890001 CM-SCE-1/2-4H-2L
 TE Part # EC6454-000 13611400	 TE Part # EC6459-000 13611405	 TE Part # EC6472-000 13611418	 TE Part # EC6479-000 13611425



 TE Part # EC6485-000 13611431	 TE Part # EC6526-000 13611907	 TE Part # EC6546-000 13611927	 TE Part # EC6552-000 13611933
 TE Part # EC6406-000 13611101	 TE Part # EC6475-000 13611421	 TE Part # EC6481-000 13611427	 TE Part # EC6494-000 13611440
 TE Part # EC6523-000 13611904	 TE Part # EC6534-000 13611915	 TE Part # EC6541-000 13611922	 TE Part # EC6471-000 13611417

Customers Also Bought

 TE Part #114017-ZZ SEALING PLUG, SIZE 12/16, WHT	 TE Part #CAT-AM71-CH8172 AMP SUPERSEAL 1.5MM, CONNECTOR HOUSING	 TE Part #281934-2 SINGLE WIRE SEAL	 TE Part #CAT-D48-ST273 DEUTSCH Solid Contacts
 TE Part #DT04-2P REC, 2P, GRY, N	 TE Part #DT06-2S PLG, 2P, GRY, N	 TE Part #CAT-D487-W416 Wedge locks: DEUTSCH DT	

Documents

4-160970-1

Standard Cable Tie, Bag, 18.5 lbf Tensile Strength, 82 Newton Tensile Strength, 200 mm [7.9 in] Length, 2.6 mm [.102 in] Width, Natural



Product Drawings

CABLE TY 200X2.6 NAT

English

Datasheets & Catalog Pages

CABLE TIES

English