
BES 516-324-G-E4-C-S4-00,3 BES00P2





- PNP
- Normally open (NO)
- 2.00 mm
- Flush (shielded)

■ Cable with connector, PUR, 0.30 m M12x1-S04









IND. CONT. EQ
81U2
US for use in the secondary of a class 2 source of supply
Environmental - Type 1 Enclosure



2.5 V


General attributes

Approvals / Conformity

Basic standard Enclosure Type per IEC 60529 Function indicator Operating distance marking Polarity reversal protected Power indicator Protection Class Short circuit protected

Electrical attributes Connection type

Eff. operating current le Eff. operating voltage Ue DC Electrical version Load capacitance max. (at Ue) Max. no-load cur. lo undamped Minimum operating current Im No-load current lo damped max. Operating voltage UB max. DC [V] Operating voltage UB min. DC [V] Rated insulation voltage Ui Rated short circuit current Ripple max. (% of Ue) Switching freq. f max. (at Ue) Switching function Switching output



CE cULus EAC IEC 60947-5-2 IP68 according to BWN PR 20 Yes Yes No Yes 830 a

Cable with connector 200 mA 24.0 V DC, direct current $0.500\,\mu F$ 3.0 mA 0 mA 9.0 mA 30 0 V 10.0 V 250 VAC 100 A 15 % 1500 Hz Normally open (NO)



Voltage drop static max.

Mechanical attributes
Ambient temperature Ta max. 70 °C -25 °C 1.60 mm Ambient temperature Ta min. Assured operating distance Sa Cable diameter D max. 3.1 mm Cable jacket material PUR Cable length 0.30 m Connector type M12x1-S04 Depth 30.0 mm Diameter d1 M08x1 Eff. operating distance Sr 2.00 mm Housing material Stainless steel Mech. installation condition Flush (shielded) Mounting length 29.0 mm Rated operating distance Sn [mm] 2.00 mm PBT Sensing face material Tightening torque 8 Nm

Remarks

Embeddable: See installation notes for inductive sensors with extended switching

The sensor is functional again after the overload has been eliminated.

For further information on MTTF/B10d, please refer to the MTTF / B10d Certificate.

Specification of the MTTF value and the B10d value do not represent any binding quality and/or life expectancy guarantees.