



 PRODUCT-DETAILS

OT160G30

OT160G30 SWITCH-DISCONNECTOR



General Information

Extended Product Type	OT160G30
Product ID	1SCA138207R1001
EAN	6417019666174
Catalog Description	OT160G30 SWITCH-DISCONNECTOR
Long Description	3-pole, front operated, base mounted switch-disconnector with protected clamp terminals, handle and shaft are not included

ABB EcoSolutions

End Of Life Disassembling Instructions	1SCC301116M0201
Environmental Information	1SCC301267D0201
Environmental Product Declaration - EPD	1SCC301281D0201

Material Compliance

Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
---	-----------------

REACH Declaration	1SCC011021D0201
RoHS Declaration	1SCC011020D0201
RoHS Information	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
Toxic Substances Control Act - TSCA	1SCC011025D0201

Popular Downloads

Data Sheet, Technical Information	1SCC301020C0201
Instructions and Manuals	1SCC301089M0204
Mechanical Drawings	OT160G3_model.igs
Environmental Product Declaration - EPD	1SCC301281D0201

Environmental

Degree of Protection	Front IP20
Environmental Information	1SCC301267D0201
Pollution Degree	3

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85365080
Country or Territory of Origin	Finland

Dimensions

Product Net Width	123 mm
Product Net Height	130 mm
Product Net Depth / Length	73 mm
Product Net Weight	0.8 kg

Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	160 mm 6.3 in
Package Level 1 Depth / Length	244 mm 9.6 in
Package Level 1 Height	96 mm 3.8 in
Package Level 1 Gross Weight	0.9 kg 1.9 lb
Package Level 1 EAN	6417019666174

Technical

Cable Cross-Section	Cu 10 ... 70 mm ²
Conventional Free-air Thermal Current (I_{th})	$\Theta = 40$ °C 160 A
Conventional Thermal Current (I_{the})	Fully Enclosed 160 A
Degree of Protection	Front IP20

Distance Between Phases	Standard
Handle Type	Handle and shaft not included
Mechanical Durability	20000
Mounting Type	Base mounting
Number of Poles	3P
Operating Mode	Front and Side
Pollution Degree	3
Position of Line Terminals	Top In - Bottom Out Bottom In - Top Out
Power Loss	at Rated Operating Conditions per Pole 6.5 W
Rated Conditional Short-Circuit Current (I_{nc})	(200 A fuse, 500 V) 100 kA (200 A fuse, 690 V) 50 kA
Rated Impulse Withstand Voltage (U_{imp})	12 kV
Rated Insulation Voltage (U_i)	acc. to IEC/EN 60664-1 1000 V
Rated Operational Current AC-21A (I_e)	(380 ... 415 V) 160 A (500 V) 160 A (690 V) 160 A
Rated Operational Current AC-22A (I_e)	(380 ... 415 V) 160 A (500 V) 160 A (690 V) 160 A
Rated Operational Current AC-23A (I_e)	(380 ... 415 V) 160 A (500 V) 160 A (690 V) 160 A
Rated Operational Power AC-23A (P_e)	(220 ... 240 V) 45 kW (400 ... 415 V) 75 kW (500 V) 90 kW (690 V) 132 kW
Rated Operational Voltage	Main Circuit 1000 V
Rated Short-Circuit Making Capacity (I_{cm})	(690 V) 12 kA
Rated Short-time Withstand Current Low Voltage (I_{cw})	for 1 s 4 kA
Special Functions	No
Standards	IEC 60947-3 / UL 98 / CSA C22.2 NO.4
Switches Operating Mechanism	Mechanism at the End of the Switch 30 (Right Side)
Terminal Type	Screw Terminals
Tightening Torque	acc. IEC 60947-1 6 N·m

Technical UL/CSA

Maximum Operating Voltage UL/CSA	600 V
Ampere Rating	125 A
Horsepower Rating UL/CSA	(240 V AC) Single Phase 20 Hp (440 ... 480 V AC) Single Phase 30 Hp
Tightening Torque	acc. IEC 60947-1 6 N·m
Tightening Torque UL/CSA	53 in·lb

Certificates and Declarations

A2L Certificate - IEC	1SCC301336D0201
ATEX Certificate	No certification needed
Declaration of Conformity - CE	1SCC301210D2701
DNV GL Certificate	1SCC301174D0204
UL Certificate	cULus certificate OT160G
VDE Certificate	No certification needed

External Classifications and Standards

Object Classification Code	Q
ETIM 9	EC000216 - Switch disconnecter (low voltage)
ETIM 10	EC000216 - Switch disconnecter (AC)
UNSPSC	39122233
IDEA Granular Category Code (IGCC)	5290 >> Disconnect switch
eClass	V11.1 : 27371403
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Categories

Low Voltage Products and Systems → Switches → Switch Disconnectors

