



Part Number : [351820192](#)
Product Description : VersaBlade Terminal Position Assurance (TPA) Retainer, 1 Circuit, Red
Series Number : 35182
Status : Active
Product Category : Connector Accessories



Documents & Resources

Drawings

[351820192 sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[351500000AS ENG-000.pdf](#)

[351500000AS KOR-000.pdf](#)

[PK-35182-001-001.pdf](#)

[PS-35150-001-001.pdf](#)

[PS-35182-003-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)8585-DC (23 Jan 2024)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Accessories
Series	35182
Description	VersaBlade Terminal Position Assurance (TPA) Retainer, 1 Circuit, Red
Component Type	Terminal Position Assurance
Product Name	VersaBlade
UPC	800754249836

Physical

Circuits (Loaded)	1
Circuits (maximum)	1
Color - Resin	Red
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	0.106/g
Number of Rows	1
Packaging Type	Bag
Temperature Range - Operating	-40° to +120°C

Mates With / Use With

Use with Part(s)

Description	Part Number
VersaBlade Hybrid Receptacle Housing, without Mounting Ears, 1 Circuit, Natural	<u>351500100</u>
VersaBlade Hybrid Receptacle Housing, without Mounting Ears, 1 Circuit, Natural, Glow-Wire Capable	<u>351500109</u>
VersaBlade Hybrid Receptacle Housing, with Mounting Ears, 1 Circuit, Natural	<u>351500110</u>
VersaBlade Hybrid Plug Housing, 1 Circuit, Positive Lock, Natural	<u>351510110</u>
VersaBlade Hybrid Plug Housing, 1 Circuit, Positive Lock, Natural, Glow-Wire Capable	<u>351510119</u>