

Linetrimmer XGT®

UR008G

40Vmax • 0 - 6 000 / 0 - 4 600 / 0 - 4 000 min⁻¹

Powerful XGT® Grass trimmer with Loop handle for various applications.

UR008G has a brushless motor and 3 - speed (Low/ Medium/High) motor system. Reverse rotation system allows operator to quickly clear trimmer head / blade of entangled grass and weeds. Soft start feature for added motor protection.



XGT **BL** **ADT** **AFT**
MOTOR

Technical specifications

Voltage XGT	✓
Nominal Battery Voltage	40 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
No load speed	0 - 4000 / 4600 / 6000 min ⁻¹
Cutting width	305 / 430 mm
Spindle Thread	M10 x 1,25 LH
Handle Type	L
Sound Power Level (L _{WA})	91,9 dB(A)
Sound Pressure Level (L _{pA})	79,0 dB(A)
Noise Uncertainty (K Factor)	1,6 dB(A)
Product net weight	4,3 kg
Tool weight with battery	5,0 - 6,2 kg
Product Dimensions (L x W x H):	1803 x 224 x 300 mm
Nylon line- Diameter	2,0 / 2,4 mm

User benefits

- ADT (Automatic torque Drive Technology) adjusts speed and torque during operation for optimum performance
- Active Feedback sensing Technology (AFT) stops the engine if the rotation suddenly stops
- Rear end mounted motor makes the tool balance similar to engine grass trimmers
- Constant speed control maintains constant speed under load
- 3-speed options (Low / Medium / High) allows the operator to match speed to application
- Soft start feature for added motor protection
- Battery protection circuit protects against overloading, over-discharging and over-heating

Link to product - www.makita.uk.com



Related products

Other

User manual

Parts drawing