




Test Probe 130

TE Internal #: 3-582118-5

Gold (Au), Test Probe 130, Test Probe Receptacles

[View on TE.com >](#)

Connectors > Connector Accessories > Test Probe Receptacles



Profile Height from PCB: 5.84 mm [.23 in]

Funnel Entry: Without

Contact Mating Area Plating Material: Gold (Au)

Features

Product Type Features

Connector & Contact Terminates To	Printed Circuit Board
Test Probe Hole Location	Side Entry
Connector System	Cable-to-Board
Funnel Entry	Without

Configuration Features

Number of Positions	1
Number of Mounting Legs	2

Body Features

Primary Product Color	Green
-----------------------	-------

Contact Features

Contact Current Rating (Max)	4.75 A
Contact Base Material	Beryllium Copper
Contact Mating Area Plating Material	Gold (Au)

Termination Features

Termination Post & Tail Length	3.3 mm[.13 in]
--------------------------------	----------------

Mechanical Attachment



Connector Mounting Type	Board Mount
-------------------------	-------------

Housing Features

Housing Material	Nylon GF
------------------	----------

Dimensions

Profile Height from PCB	5.84 mm[.23 in]
-------------------------	-----------------

Usage Conditions

Operating Temperature Range	-55 – 85 °C[-67 – 185 °F]
-----------------------------	---------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 240°C

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts







TE Part # 1-380736-9
TEST PROBE REC180 BI WHT GPBR




TE Part # 3-582118-9
TEST PROBE REC130 BI WHT GPBR



TE Part # 3-582118-0
TEST PROBE REC130 BI BLK GPBR




TE Part # 3-582118-2
TEST PROBE REC130 BI RED GPBR




TE Part # 3-582118-4
TEST PROBE REC130 BI YEW GPBR



TE Part # 350180-9
TEST PROBE REC130 SPCL WHT GPBR




TE Part # 3-582119-0
TEST PROBE REC130 TRI-MT BLK GPBR



TE Part # 3-582118-6
TEST PROBE REC130 BI BLU GPBR

Also in the Series | [Test Probe 130](#)



[Test Probe Receptacles\(17\)](#)


Customers Also Bought



TE Part #YDIV44E17-35SBV001
RECP ASSY




TE Part #1318127-1
DYNAMIC D2100 HDR V ASSY 20P



TE Part #503123-000
DK-621-0412-S



TE Part #61764-1
RING CRIMP 20-16 AWG BR



TE Part #241251-000
DK-621-0440-4S



Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_3-582118-5_AP.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_3-582118-5_AP.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_3-582118-5_AP.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

PRINTED CIRCUIT BOARD TERMINALS AND DISCONNECTS

English

Product Specifications

Application Specification

English

Test Probe Receptacle Contacts

English