

FAG


23218-E1-XL-K-TVPB

Spherical Roller Bearing

Spherical roller bearings 232...-E1-K, main dimensions to DIN 635-2, with tapered bore, taper 1:12

X-life

Technical information




Your current product variant

Design	E1	without central rip
Bore type	K	Tapered, taper 1:12
Cage	TVPB	Plastic cage
Radial internal clearance	CN (Group N)	Normal internal clearance
Relubrication feature	Standard	

Main Dimensions & Performance Data

d	90 mm	Bore diameter
D	160 mm	Outside diameter
B	52.4 mm	Width
C _r	445,000 N	Basic dynamic load rating, radial
C _{0r}	520,000 N	Basic static load rating, radial
C _{ur}	50,000 N	Fatigue load limit, radial
n _G	4,250 1/min	Limiting speed
n _{gr}	2,650 1/min	Reference speed
≈m	4.111 kg	Weight





Mounting dimensions

d _{a min}	101 mm	Minimum diameter shaft shoulder
D _{a max}	149 mm	Maximum diameter of housing shoulder
r _{a max}	2 mm	Maximum recess radius
B _{a min}	18 mm	Minimum cavity width of the sleeve
d _{a max}	104 mm	Maximum diameter of shaft shoulder
d _{b min}	100 mm	Minimum cavity diameter of the sleeve

Dimensions

r _{min}	2 mm	Minimum chamfer dimension
D ₁	140 mm	Bore diameter outer ring
d ₂	104.1 mm	Raceway diameter of the inner ring
d _s	3.2 mm	Diameter lubrication hole
n _s	6.5 mm	Width of lubricating groove

Temperature range

T _{min}	-30 °C	Operating temperature min.
T _{max}	120 °C	Operating temperature max.

Calculation factors

e	0.31	Limiting value of Fa/Fr for the applicability of diff. Values of factors X and Y
Y ₁	2.2	Dynamic axial load factor
Y ₂	3.27	Dynamic axial load factor
Y ₀	2.15	Static axial load factor

Additional information

H2318	Adapter sleeve
AHX3218	Withdrawal sleeve



Characteristics

-  Radial load
-  Axial load in one direction
-  Axial load in two directions
-  Grease Lubrication
-  Oil Lubrication
-  Not sealed
-  Static angular error and misalignment
-  Dynamic angular error and misalignment