



Main

Range	Merten
Product or component type	Presence detector
Device presentation	Complete product
Colour tint	Polar white (RAL 9010)

Complementary

Device application	Lighting
Technology type	Electronic
Device mounting	Surface
Material	Thermoplastic
Surface finish	Glossy
[Ue] rated operational voltage	230 V
Network type	AC
Network frequency	50/60 Hz
Rated current	16 A
Protection type	Creep zone protection
Light intensity adjustment	3...1000 lux
Time delay range	1 s...8 min
Mounting height	2.5 m
IP degree of protection	IP55

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins