


## Technical data

### 29412E

Thrust spherical roller bearings



#### VISUAL (S)



## PRODUCT DEFINITION

|                                                              |          |
|--------------------------------------------------------------|----------|
| <b>Brand</b>                                                 | SNR      |
| <b>d - Internal diameter of shaft washer</b>                 | 60 mm    |
| <b>D - Housing washer outer diameter</b>                     | 130 mm   |
| <b>D1 - Inner diameter housing washer</b>                    | 88 mm    |
| <b>d1 - External diameter shaft washer</b>                   | 112,3 mm |
| <b>T - Thrust bearing height</b>                             | 42 mm    |
| <b>C - Housing washer width</b>                              | 20,5 mm  |
| <b>B - Shaft washer width</b>                                | 27 mm    |
| <b>B2 - Distance large face of shaft washer / metal cage</b> | 37 mm    |
| <b>a - Charge load application point</b>                     | 38 mm    |
| <b>Cage material</b>                                         | Tôle     |
| <b>Mass</b>                                                  | 2,47 kg  |

## PRODUCT PERFORMANCE

|                                            |              |
|--------------------------------------------|--------------|
| <b>Ca - Dynamic axial load rating</b>      | 334000000 mN |
| <b>C0a - Static axial load rating</b>      | 955000000 mN |
| <b>Cua - Limit axial load rating</b>       | 116000000 mN |
| <b>N lim - Oil lubrication limit speed</b> | 15600 °/s    |
| <b>N ref - Reference thermal speed</b>     | 15600 °/s    |
| <b>N lim - Mechanical Limit Speed</b>      | 30600 °/s    |
| <b>Tmin - Min operating temperature</b>    | 233,15 °K    |
| <b>Tmax - Max operating temperature</b>    | 473,15 °K    |

## BEARING FREQUENCIES

|                                                             |          |
|-------------------------------------------------------------|----------|
| <b>BPFO - Over rolling frequency on outer ring (60 rpm)</b> | 7.604 Hz |
|-------------------------------------------------------------|----------|



**NTN Europe**

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00  
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072  
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

## BEARING FREQUENCIES

|                                                                 |          |
|-----------------------------------------------------------------|----------|
| <b>BPFI - Over rolling frequency on inner (60 rpm)</b>          | 9.396 Hz |
| <b>BSF - Over rolling frequency on rolling element (60 rpm)</b> | 5.719 Hz |
| <b>BRF - Rotational frequency - rolling element (60 rpm)</b>    | 2.86 Hz  |
| <b>FTF - Rotational frequency - cage (60 rpm)</b>               | 0.447 Hz |

## ABUTMENT

|                                                            |        |
|------------------------------------------------------------|--------|
| <b>ras max - Max shaft &amp; housing fillet radius</b>     | 1,5 mm |
| <b>rs - Min fillet radius</b>                              | 1,5 mm |
| <b>Da max - Max shoulder diameter OR</b>                   | 117 mm |
| <b>da min - Min shoulder diameter IR</b>                   | 90 mm  |
| <b>db1 - Maximum diameter of the shaft washer shoulder</b> | 67 mm  |
| <b>db2 - Max spacer diameter</b>                           | 67 mm  |

