




FAG

32316-B

Tapered roller bearing

Tapered roller bearings 323, main dimensions to DIN ISO 355 / DIN 720, separable, adjusted or in pairs

Technical information



Your current product variant

Tolerance class	PN	Normal (ISO 492:2014)
Heat treatment	Standard	
Cage	Standard	Sheet steel cage, window cage, roller-guided
Internal design	B	Increased contact angle
Quality level	Standard	
Number of rolling element rows	1	Single-row design

Main Dimensions & Performance Data

d	80 mm	Bore diameter
D	170 mm	Outside diameter
B	58 mm	Width, inner ring
C	48 mm	Width, outer ring
T	61.5 mm	Width, total
C <sub>r</sub>	355,000 N	Basic dynamic load rating, radial
C <sub>0r</sub>	510,000 N	Basic static load rating, radial
C <sub>ur</sub>	62,000 N	Fatigue load limit, radial
n <sub>G</sub>	4,100 1/min	Limiting speed
n <sub>gr</sub>	3,300 1/min	Thermal speed rating
≈m	6.537 kg	Weight



Mounting dimensions

d <sub>a</sub> max	96 mm	Maximum diameter of shaft shoulder
d <sub>b</sub> min	92 mm	Minimum diameter of shaft shoulder
D <sub>a</sub> min	130 mm	Minimum diameter of housing shoulder
D <sub>a</sub> max	158 mm	Maximum diameter of housing shoulder
D <sub>b</sub> min	160 mm	Minimum diameter of housing shoulder
C <sub>a</sub> min	7 mm	Minimum axial space
C <sub>b</sub> min	13.5 mm	Minimum axial space
r <sub>a</sub> max	3 mm	Maximum fillet radius of shaft
r <sub>b</sub> max	2.5 mm	Maximum fillet radius of housing

Dimensions

r <sub>1, 2</sub> min	3 mm	Minimum chamfer dimension of inner ring back face
r <sub>3, 4</sub> min	2.5 mm	Minimum chamfer dimension of outer ring back face
a	49 mm	Distance between the apexes of the pressure cones
d <sub>1</sub>	126.85 mm	Guidance rib diameter of inner ring

Temperature range

T <sub>min</sub>	-30 °C	Operating temperature min.
T <sub>max</sub>	120 °C	Operating temperature max.

Calculation factors






e	0.55	Limiting value of Fa/Fr for the applicability of diff. Values of factors X and Y
Y	1.1	Dynamic axial load factor
Y <sub>0</sub>	0.6	Static axial load factor

Additional information

T5GD080	Comparative designation to ISO 10317 and ISO 355
---------	--



Characteristics

-  Radial load
-  Axial load in one direction
-  Grease Lubrication
-  Oil Lubrication
-  Not sealed