

FEATURES

- 5 mm tinted diffused epoxy lens.
- Various voltages
- Recessed or prominent bezel style
- Longevity and low power consumption
- Solder pin terminals

RS PRO Green Indicator, 2 V dc, 8mm Mounting Hole Size, Lead Pins Termination, IP67

RS Stock No.: 205-555



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



Product Description

Brought to you by RS Pro, a high quality range of LED indicators. Each indicator has a compact and durable build, complimented by their IP67 Rating. Pin terminals are attached to the indicators for convenience and easy installation. Whether the application is a signal or warning light, or purely for display purposes, there are various colours to suit your needs. All models are highly reliable and excellent quality.

General Specifications

Light Output Colour	Green
Lamp Type	LED
Termination Type	Lead Pins
Туре	Panel Mount
Bezel Style	Prominent
Bezel Colour	Chrome
Intensity	40 mcd
Type Of Illumination	Fixed Light
LED Colour	Green
Viewing Angle	30-100°
Life Expectancy	100000hours
Applications	Fixed to PCB circuit boards mounted; Switches; Pushbuttons; Used as vehicle indicators

Electrical Specifications

Voltage Rating	2V dc
Current Rating	20mA
Voltage Tolerance	10%



Mechanical Specifications

Mounting Hole Size	8mm
Length	30.5mm
Torque	20cNm to 25cNm
Lamp Size	5mm

Operation Environment Specifications

Temperature Rating -40 to 85°C

Protection Category

IP Rating	IP67

Approvals

Compliance/Certifications	EN61340
Compilarios, Committationic	21401010












TECHNICAL SPEC	IFICATIONS	
Voltage	Operating Voltage	Operating Current
	(Min to Max)	(Typical All Types)
02 (No Resistor)	1.8 to 3.3VDC	20mA max*
6VDC	5.4 to 6.6VDC	20mA
12VDC	10.8 to 13.2VDC	20mA
24VDC	21.6 to 26.4VDC	20mA
28VDC	25.2 to 30.8VDC	20mA
110VAC	99 to 121VAC	6mA
220VAC	207 to 253VAC	3mA





Indicators





Standard LED Intensity	Prominent and Recessed	Flush	Forward Voltage
HE Red	80mcd	8mcd	2.0V
Green	60mcd	6mcd	2.2V
Yellow	50mcd	6mcd	2.1V
Blue	1600mcd	50mcd	3.3V
White	1600mcd	500mcd	3.3V
Orange	60mcd	110mcd	2.2V
Bi-color (Typical) (Red/Green)	14/30mcd	15/10mcd	2.0V/2.2V
Tri-color (Typical) (Red/Green/Yellow)	60/15/13mcd	15/10/6mcd	2.0V/2.2V/2.1V
Bi-color - The co	lor is changed by reversing the po	plarity of the supply volt	tage.
Tri-color - The indicato	r has red and green LEDs, when b	oth connected yellow i	is produced.
Super Bright LED	Prominent and Recessed	Flush	Forward Voltage
HE Red	5,000mcd	1,300mcd	2.2V
Green	10,000mcd	1,200mcd	3.3V
	4.000	350mcd	2.0V
Yellow	4,000mcd	33011100	2.01
	2,200mcd	280mcd	3.3V
Yellow Blue White			
Blue White	2,200mcd	280mcd	3.3V
Blue White Orange	2,200mcd 2,500mcd	280mcd 950mcd	3.3V 3.3V
Blue White Orange Hyper Bright LED	2,200mcd 2,500mcd 4,000mcd	280mcd 950mcd 500mcd	3.3V 3.3V 2.2V
Blue White Orange Hyper Bright LED HE Red	2,200mcd 2,500mcd 4,000mcd Prominent and Recessed	280mcd 950mcd 500mcd	3.3V 3.3V 2.2V Forward Voltage
Blue	2,200mcd 2,500mcd 4,000mcd Prominent and Recessed 6,000mcd	280mcd 950mcd 500mcd Flush 980mcd	3.3V 3.3V 2.2V Forward Voltage 2.2V


PROMINENT BEZEL























Indicators

