


EA**BSP Swivel Female****with O-Ring (60° Cone)**

BS 5200 – ISO 12151-6 – DKOR

***New 3S-Fitting-Design**

Part Number	Hose I.D.				Thread BSP	A mm	B mm	H mm	W mm	Max WP MPa
	DN	Inch	Size	mm						
1EA48-2-4	6	1/4	-4	6.4	1/8x28	41	17		14	63.0
1EA48-4-4	6	1/4	-4	6.4	1/4x19	40	17		19	45.0
1EA48-4-5	8	5/16	-5	7.9	1/4x19	45	21		19	45.0
1EA48-6-4	6	1/4	-4	6.4	3/8x19	49	26		22	45.0
1EA48-6-5	8	5/16	-5	7.9	3/8x19	50	25		22	45.0
1EA48-6-6	10	3/8	-6	9.5	3/8x19	43	20		22	45.0
1EA48-8-6	10	3/8	-6	9.5	1/2x14	51	28		27	42.0
1EA48-6-8	12	1/2	-8	12.7	3/8x19	46	22		22	45.0
1EA48-8-8	12	1/2	-8	12.7	1/2x14	45	22		27	42.0
1EA48-8-8C	12	1/2	-8	12.7	1/2x14	45	22		27	42.0
1EA48-10-10*	16	5/8	-10	15.9	5/8x14	50	27	24	30	42.0
1EA48-12-10	16	5/8	-10	15.9	3/4x14	54	29		32	42.0
1EA48-12-12*	19	3/4	-12	19.1	3/4x14	53	29	27	32	42.0
1EA48-16-12	19	3/4	-12	19.1	1x11	61	35		41	42.0
1EA48-16-16*	25	1	-16	25.4	1x11	66	38	32	41	42.0
1EA48-16-16C*	25	1	-16	25.4	1x11	61	31		41	42.0
1EA48-20-20	31	1 1/4	-20	31.8	1 1/4x11	78	31		50	35.0
1EA48-24-24	38	1 1/2	-24	38.1	1 1/2x11	72	34		55	30.0
1EA48-32-32	50	2	-32	50.8	2x11	81	33		70	25.0



Hose fittings are delivered with ozone resistant Nitrile (NBR) O-ring as a standard version. Working temperature from -40 °C up to +105 °C.
Hose fittings with special O-rings (Viton or EPDM) available on request. See the O-ring dimensions and part numbers in the 4400 catalogue.

* Suffix C = Stainless

* Crimp hex version

EB**BSP Swivel Female****with O-Ring****45° Elbow (60° Cone)**

BS 5200 – ISO 12151-6 – DKOR 45°



Part Number	Hose I.D.				Thread BSP	A mm	B mm	E mm	W mm	Max WP MPa
	DN	Inch	Size	mm						
1EB48-4-4	6	1/4	-4	6.4	1/4x19	57	34	14	19	45.0
1EB48-6-6	10	3/8	-6	9.5	3/8x19	69	46	17	22	45.0
1EB48-8-8	12	1/2	-8	12.7	1/2x14	71	48	20	27	42.0
1EB48-12-12	19	3/4	-12	19.1	3/4x14	89	63	27	32	42.0
1EB48-16-16	25	1	-16	25.4	1x11	112	82	33	41	42.0
1EB48-32-32	50	2	-32	50.8	2x11	210	161	66	70	25.0

Hose fittings are delivered with ozone resistant Nitrile (NBR) O-ring as a standard version. Working temperature from -40 °C up to +105 °C.
Hose fittings with special O-rings (Viton or EPDM) available on request. See the O-ring dimensions and part numbers in the 4400 catalogue.