



Fuse-link, low voltage, 560 A, AC 550 V, DC 400 V, BS88/C2, 74 x 210 mm, gL/gG, BS

Catalog No. **FF560**

### Delivery program

Product range			Fuse
Basic function			Fuse-link
Field of application			low voltage
Rated current	I	A	560
Rated voltage			AC 550 V DC 400 V
Construction size			BS88/C2
Size			74 x 210 mm
Utilization category			gL/gG
Breaking Capacity		kA	80
usable for size/applications			general industrial applications
Standard/Approval			BS
Shape			centre-bolted tags
Material			Ceramic body
Standards/Regulations			BS88-2 IEC 60269-2

### Technical data ETIM 7.0

Circuit breakers and fuses (EG000020) / Low Voltage HRC fuse (EC000055)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse inserts / Low-Voltage HRC fuse (ecl@ss10.0.1-27-14-20-05 [AFZ800015])			
Construction size			Other
Rated current		A	560
Rated voltage		V	550
Voltage type			AC/DC
Rated switching capacity		kA	80
Utilization category			Other
Type of fuse status indicator			None
Insulated metal gripping lugs (IMGL)			No

### Additional product information (links)

Product datasheet (pdf)	<a href="http://www1.cooperbusmann.com/pdf/a93c84da-0cf7-404d-ad7b-06cb906be543.pdf">http://www1.cooperbusmann.com/pdf/a93c84da-0cf7-404d-ad7b-06cb906be543.pdf</a>
-------------------------	---