

LH-SE 250K-ST

Pressed steel swivel castor, heavy duty design, with top plate fitting, with brake system 'stop-top', heavy duty wheel, with 'Blickle EasyRoll' elastic solid rubber tyres, with steel wheel centre

EAN 4047526010898

ID 10892

Customs tariff number 87169090



Bracket: LH series

- strong pressed steel, zinc-plated, blue-passivated, Cr6-free
- heavy fork and top plate
- double ball bearing in the swivel head
- bolted and secured central kingpin, extremely strong
- particularly resistant to shocks and impact due to **four specially-shaped, hardened bearing seats**

Wheel: SE series

- tyre: high-quality elastic solid rubber "Blickle EasyRoll" in smooth rolling quality, hardness 65 Shore A, colour black
- wheel centre: thick-walled pressed steel, with tubular steel hub, lacquered, colour anthracite

Other features:

- chemical resistance to many aggressive substances, except oils
- operating temperature: -20 °C to +80 °C, temporarily up to +100 °C, reduced load capacity over +60 °C

Technical data:

Wheel Ø (D)	☉	250 mm
Wheel width	⊥	63 mm
Load capacity at 4 km/h	⚖	850 kg
Load capacity (static)	⚖	2,125 kg
Bearing type	⦿	ball bearing
Total height (H)	⊕	295 mm
Mounting type		top plate
Plate size	📏	140 x 110 mm
Bolt hole spacing	📏	105 x 75–80 mm
Bolt hole Ø	🔧	11 mm
Offset (F)	📏	82 mm
Temperature resistance min		-20 °C
Temperature resistance max		80 °C
Tread and tyre hardness		65 Shore A
Unit weight	📏	7.1 kg
Non-marking		×
Non-staining		×
Antistatic	🔧	×
ESD		×
Electrically conductive	🔧	×
Corrosion-resistant		×
Heat-resistant	🔥	×



Tread and tyre hardness

■ ■ ■ ■ ■ 65 Shore A

Rolling resistance



■ ■ ■ ■ ■ very good

Wear resistance

■ ■ ■ ■ ■ good

Operating noise / floor surface preservation

■ ■ ■ ■ ■ very good



Suitable for autoclaves	×
Suitable for machine washing	×

Product references



Corresponding fixed castor BH-SE 250K



Corresponding swivel castor LH-SE 250K



Wheel used SE 250/25K