

Ball valve unit VAPB-A-1 1/2-F-25-F0405-PB80

Part number: 8191932

FESTO



 General operating condition

Data sheet

Feature	Value
Design	2-way ball valve Semi-rotary drive
Type of actuation	Pneumatic
Sealing principle	Soft
Mounting position	optional
Type of mounting	In-line installation
Connection Process valve	Rp1 1/2
Switching position indicator	Slot direction = flow direction
Flange hole pattern	F0405
Nominal size DN	40
Valve function	2/2
Flow direction	Reversible
Operating pressure	0.55 MPa ... 0.8 MPa
Operating pressure	5.5 bar ... 8 bar
Operating pressure	79.75 psi ... 116 psi
Nominal pressure PN	25
Breakaway torque at differential pressure, nominal pressure, process valve PN	19 Nm
Based on standard	EN 10226-1 ISO 5211
Symbol	00992011
Medium	Compressed air to ISO 8573-1:2010 [-:-:-] Inert gases Water – no water vapour Neutral fluids Other media on request
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Media temperature	-10 °C ... 200 °C
Flow rate Kv	200 m³/h
Note on materials	RoHS-compliant
LABS (PWIS) conformity	VDMA24364 zone III
Material housing	Brass, nickel-plated
Material number housing	2.0402 CW617N

Feature	Value
Material seat seal	PTFE
Material seals	HNBR PTFE
Material ball	Brass Hard-chrome-plated
Material number ball	2.0402 CW617N
Material shaft	Brass
Material number shaft	2.0401 CW614N
Product weight	5930 g
Corrosion resistance class CRC	1 - Low corrosion stress