

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Straight Grinder

PRO GGS 8 CE



Unique for powerful surface grinding in the straight grinder category

The most important data

Rated input power	750 W
No-load speed	2,500 – 8,000 rpm
Weight	1.7 kg

Part Number 0 601 222 160

Technical data

Technical data

No-load speed	2,500 – 8,000 rpm
Rated input power	750 W
Power output	420 W
Spindle collar diameter	43 mm
Weight	1.7 kg
Max. collet diameter	8 mm
Max. grinding tool diameter	50 mm
Spanner size of locking nut	19 mm
Spanner size of grinding spindle	13 mm
Max. polishing tool diameter	80 mm
Switch	Lockable Switch
Packaging dimensions (width x length x height)	155 x 495 x 105 mm
Voltage, electrical	110 V

Noise/vibration information

Surface grinding up to diameter of 25

Vibration emission value ah	2.5 m/s ²
Uncertainty K	1.5 m/s ²

Surface grinding up to diameter of 50

Vibration emission value ah	2.5 m/s ²
Uncertainty K	2.5 m/s ²



BOSCH

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- 750 W motor with soft start facilitates fast work progress
- High torque and handy design ideal for use on surfaces with flap wheels, brushes, and other accessories
- Increased user protection due to KickBack Control feature

**HEAVY
DUTY**



You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

