IEC Plug 400 VDC, Rewireable, Straight, max. Cable Diameter 9.2 mm



GP21 rewireable cord plug for 400 VDC systems up to 2.6 kW $\,$

Standard	
Sheet 2	

Description

- Plug (rewireable) :
- Screw-on mounting
- Plug , Protection class I
- Wire size 0.75-1.5mm², 18AWG-16AWG
- Cable diameter 6.4 9.2 mm

Unique Selling Proposition

- Standard form acc. to IEC TS 62735-1
- Hot plug rated for disconnecting under loads up to 2.6 kW
- Ideal for compact PDU applications with an operating temperature up
- to 105 °C

Technical Data

Ratings IEC	6.5 - 8.8A / 400 - 294 VDC max. 2.6 kW power	appliance inlet/-outlet	Standard Sheet 2 acc. to IEC TS 62735-1
Dielectric Strength	> 3 kVDC between + and - > 3 kVDC between +/- and PE (1 min)		Protection Class I , ± 200 VDC
Allowable Operation Tempe- rature	-5°C to 105°C		
Terminal	Screw terminal		
Material: Housing	Thermoplastic, black, UL 94V-0		

Approvals and Compliances

Detailed information on product approvals, code requirements, usage instructions and detailed test conditions can be looked up in Details about Approvals

SCHURTER products are designed for use in industrial environments. They have approvals from independent testing bodies according to national and international standards. Products with specific characteristics and requirements such as required in the automotive sector according to IATF 16949, medical technology according to ISO 13485 or in the aerospace industry can be offered exclusively with customer-specific, individual agreements by SCHURTER.

Approvals

The approval mark is used by the testing authorities to certify compliance with the safety requirements placed on electronic products. Approval Reference Type: GP21

Approval Logo	Certificates	Certification Body	Description
	VDE Approvals	VDE	VDE Certificate Number: pending
(i)	UL Approvals	UL	UL File Number: E502317

See below: Approvals and Compliances


Weblinks

pdf data sheet, html datasheet, General Product Information, Distributor-Stock-Check, Accessories, Mounting instruction, Detailed request for product, Landing Page, Video

GP21

Product standa	ards		
Product standards	s that are referenced		
Organization	Design	Standard	Description
IEC.	Designed according to	IEC TS 62735-1	Appliance couplers for household and similar general purposes
(!)	Designed according to	UL Subject 2695	Outline for DC rated Attachment Plugs and Outlet Devices for ICT Equip- ment installed in restricted access locations
Application sta			
Application standa	ards where the product can be used		
Organization	Design	Standard	Description
<u>IEC</u>	Designed for applications acc.	IEC/UL 60950	IEC 60950-1 includes the basic requirements for the safety of information technology equipment.
Compliances			
The product comp	olies with following Guide Lines		
Identification	Details	Initiator	Description
ROHS	RoHS	SCHURTER AG	Directive RoHS 2011/65/EU, Amendment (EU) 2015/836
(1)	China RoHS	SCHURTER AG	The law SJ / T 11363-2006 (China RoHS) has been in force since 1 March 2007. It is similar to the EU directive RoHS.
Halogen Free [#=	Halogen Free	SCHURTER AG	SCHURTER strives to offer our customers halogen free products.
REACH	REACH	SCHURTER AG	On 1 June 2007, Regulation (EC) No 1907/2006 on the Registration, Evaluation, Authorization and Restriction of Chemicals 1 (abbreviated as "REACH") entered into force.

Dimensions [mm]



All Variants

vailability for all products can be searched real-time:https://www.schurter.com/en/Stock-Check/Stock-	Color	Max. cable diameter	Max. wire size	Order Number	
vailability for all products can be searched real-time:https://www.schurter.com/en/Stock-Check/Stock-heck-SCHURTER	black	9.2 mm	3 x 1.5 mm² / 3 x 16 AWG	3-101-786	
	Most Popular. Availability for all proc	ducts can be searched real-tim	e:https://www.schurter.com/en/S	Stock-Check/Stock	
Iax. LUIQUE IUI SCIEWS. TEITIIIIIAIS. U.S INITI. CADIE CIAITIDS. U.S INITI. COVEL. U.S INITI	Check-SCHURTER	ws: Terminals: 0.5 Nm. Cable c	amps: 0.5 Nm. Cover: 0.3 Nm		

Mating Outlets/Connectors

Category / Description



Appliance Outlet Overview complete

Appliance Outlet further types to GP21

IEC Socket-Outlet 400 VDC, Snap-in Mounting, Front Side, Quick-connect or PCB Terminals

GS21