

NAVIGATOR VE-LED

Navigator VE is a compact metal formed LED sign luminaire for mounting over doorways in general applications.

- Extended life, high performance LED light source
- Energy saving **LED** control technology
- Slim, clean style
- 32m viewing distance
- Downlight panel for floor illumination below



Specification	Self-contained luminaire
	Electrical & operational
Input voltage	220-240v 50Hz
Operation	Maintained
Duration	3 hours
Battery	High temperature nickel metal hydride
Charger	Constant current
Charging monitor	Green LED
Recharge period	24 hours
Lamp	LED strip light
Lamp rating:	1w
Consumption:	NM- 12mA, M-27mA
	Construction & Installation
Cable entry	Via knockouts
Construction	Folded metal enclosure, standard finish in white epoxy
Environment	0 – 25 °C
Ingress class	IP20 for indoor use
Dimensions LWD (mm)	385 x 185 x 75
Weight (kg)	2.2
Product standards	Designed & manufactured to meet BSEN60598.2.22 product regulations
To order	Description
Product code	
VE3LS1	Escape-LED, M 3 hour duration, white trim
VEBACK	Plain back plate in white for ceiling mounting

Legend panels

ISO7010 format		Description
Code	Panel	
XEN2V31		Panel, arrow down
XEN3V31		Panel, arrow left
XEN6V31		Panel, arrow right
XEN5V31		Panel, arrow up