



**Product Data Sheet (Alt to RS 227-4994)**

**Vacuum Pump, Dia.19.1mm, 847mbar, 6.4mm Orifice**  
**S80-000-925**



Model Number	A Barrel ID in. (mm)	B in. (mm)	C Collar Length in. (mm)	D in. (mm)	E Input	F Barrel OD in. (mm)	G Collar OD in. (mm)	H in. (mm)	I Thread	J Thread
Q-VDF250	0.250 (6.4)	7/8 (22.2)	1-1/4 (31.8)	5/8 (15.9)	G1/8"	3/4 (19.1)	1-1/4 (31.8)	1-1/2 (38.1)	G1/4"	G1/4"

**Specification**

<input type="checkbox"/>	Maximum Operating Temperature	+204°C
<input type="checkbox"/>	Maximum Suction Flow	3398L/min (250 model 283L/min)
<input type="checkbox"/>	Maximum Vacuum Pressure	847mbar
<input type="checkbox"/>	Minimum Operating Temperature	-73°C
<input type="checkbox"/>	Nozzle Diameter	19.1mm
<input type="checkbox"/>	Evacuation Time (1 Litre)	1.3s
<input type="checkbox"/>	Operating Pressure	3.5bar
<input type="checkbox"/>	Silencer	Yes