

## **Tungsten carbide burr cylindrical with radius end WRC dia. 08x20 mm shank dia. 6 mm Z3P universal medium cross cut**



**Tungsten carbide burr cylindrical with radius end WRC dia.  
08x20 mm shank dia. 6 mm Z3P universal medium cross  
cut**

Item number: [21105126](#)

EAN: [4007220046302](#)

Cut 3 PLUS is cross cut and especially well-suited to machining of cast iron, steel, stainless steel (INOX), nickel-based alloys and titanium alloys. It is characterized by its high stock removal rate.

Tungsten carbide burrs for general applications are suitable for fine and coarse stock removal on the key materials used in industrial manufacturing. They provide a good stock removal rate and are not specific to a particular material.

Cylindrical burr with radius end according to DIN 8032 with cut conforming to DIN 8033. Combination of cylindrical and ball-shaped geometries.

---

## Technical information

|   |                     |
|---|---------------------|
| Cut   | 3 PLUS              |
| Dia. external   | 8 mm                |
| Dia. shank  | 6 mm                |
| Length, cut   | 20 mm               |
| Length, total   | 60 mm               |
| RPM, grey cast iron, white cast iron                            | 18.000 - 24.000 RPM |
| RPM, hardened, heat-treated steels over 1,200 N/mm <sup>2</sup> | 10.000 - 14.000 RPM |
| RPM, high-temperature-resistant materials                       | 10.000 - 18.000 RPM |
| RPM, rust and acid-resistant steels                             | 10.000 - 14.000 RPM |
| RPM, steels up to 1,200 N/mm <sup>2</sup>                       | 18.000 - 24.000 RPM |

## Advantages

- ✔ Good stock removal rate through optimum matching of tungsten carbide, geometry, cut and available coating.
- ✔ Long tool life.
- ✔ The highly accurate concentricity enables impactfree working without creating chatter marks. This considerably reduces wear on the tool and tool drive.
- ✔ High surface quality.

## Recommendations for use

- ✔ To ensure costeffective use of burrs, use a higher rotational speed and cutting speed. Use burrs with a shank diameter of 6 mm with drives with a power output from 300 watts.

## Materials that can be worked

- ✓ Annealed cast iron
  - ✓ Black annealed cast iron (GTS, GJMB)
  - ✓ Brass
  - ✓ Bronze
  - ✓ Case-hardened steels
  - ✓ Cast iron
  - ✓ Cast steel
  - ✓ Cobalt-based alloys
  - ✓ Grey/nodular cast iron (GG/GJL, GGG/GJS)
  - ✓ Hard aluminium alloys
  - ✓ Hardened, heat-treated steels over 1.200 N/mm<sup>2</sup> (< 38 HRC)
  - ✓ High-temperature-resistant materials
  - ✓ Nickel-based alloys (e.g. Inconell and Hastelloy)
  - ✓ Stainless steel (INOX)
  - ✓ Steel
  - ✓ Steel, cast steel
  - ✓ Steels over 700 N/mm<sup>2</sup> (> 220 HB)
  - ✓ Steels up to 1,200 N/mm<sup>2</sup> (< 38 HRC)
  - ✓ Steels up to 700 N/mm<sup>2</sup> (< 220 HB)
  - ✓ Tool steels
  - ✓ White annealed cast iron (GTW, GJMW)
-

## Applications

- ✓ Cutting out holes
  - ✓ Deburring
  - ✓ Leveling
  - ✓ Milling
  - ✓ Milling out
  - ✓ Surface work
  - ✓ Work on weld seams
- 

## Drive types

- ✓ Automated centres
  - ✓ Drive spindle
  - ✓ Flexible shaft drive
  - ✓ Straight grinder
  - ✓ Tool machine
- 



August Rüggeberg GmbH & Co. KG  
Hauptstraße 13  
51709 Marienheide

+49 2264 9-0

+49 2264 9-400

[info@pferd.com](mailto:info@pferd.com)