




**Part Number :** [480372100](#)

**Product Description :** Universal Serial Bus (USB) Shielded I/O Plug, Type A, Right-Angle, Surface Mount, Straight Tab 4.80mm, 0.76µm Gold (Au) Plating, PCB Thickness 1.60mm, Tape on Reel Package, Lead-Free

**Series Number :** 48037

**Status :** Active

**Product Category :** I/O Connectors



---

## Documents & Resources

### Drawings

[480372100\\_sd.pdf](#)

[PK-48037-210-002.pdf](#)

### 3D Models and Design Files

[480372100\\_stp.zip](#)

### Specifications


[PS-48037-001-001.pdf](#)

[TS-48037-001-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

## Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	I/O Connectors
Series	48037
Description	Universal Serial Bus (USB) Shielded I/O Plug, Type A, Right-Angle, Surface Mount, Straight Tab 4.80mm, 0.76µm Gold (Au) Plating, PCB Thickness 1.60mm, Tape on Reel Package, Lead-Free
Application	Wire-to-Board
Comments	Straight Tab 4.80mm
Component Type	Plug
Product Name	USB
Standard	USB 2.0
Type	A
UPC	822350302760

### Electrical

Current - Maximum per Contact	1.5A
Shielded	Yes
Shield Type	Full Shield
Voltage - Maximum	150V AC (RMS)

### Physical

Circuits (Loaded)	4
Circuits (maximum)	4
Color - Resin	Black
Gender	Male
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Mounting Style	Top-Mount
Net Weight	1.908/g
Number of Rows	1
Orientation	Right Angle
Packaging Type	Embossed Tape on Reel
Panel Mount	Yes
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Pitch - Mating Interface	2.00mm, 2.50mm
Pitch - Termination Interface	2.00mm, 2.50mm
Plating min - Mating	0.762µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Ports	1
Temperature Range - Operating	-20° to +85°C
Termination Interface Style	Surface Mount
Waterproof / Dustproof	No

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
Mates With	USB Type A Receptacle